



Valve Connector Cordset


VMC-2+P/V2-5M-PVC

- Valve connector according EN 175301-803 A/ISO 4400
- Varistor as a protective circuit
- Built-in LED, as operating and function indicator
- Moulded seal
- freely selectable cable models due to bridged protective earth
- Flame resistant cable
- Oil resistant
- Immunity to vibration

Valve connector Form C, varistor LED 2-pin+PE, PVC cable black

Dimensions





Technical Data


General specifications		
Connector 1		
Connection		Valve connector DIN
Construction type		form C
Style		angled
Locking		screw connection
Number of pins		2 + PE
Connector 2		
Connection		cable end
Customization		sheath stripped 50 mm
Indicators/operating means		
LED yellow		Operating display
Electrical specifications		
Operating voltage	U_B	max. 24 V AC/DC
Operating current	I_B	max. 4 A
Suppression		Varistor
Conformity		


Release date: 2025-02-04 Date of issue: 2025-02-04 Filename: 247580_eng.pdf

Technical Data

Degree of protection		EN 60529
Plug connection		Valve connector : DIN EN 175301-803
Flammability		DIN VDE 0482 , DIN EN 50265-2-1 , UL 94
Oil resistance		DIN EN 60811-2-1
Ambient conditions		
Ambient temperature		
Plug connector		-20 ... 85 °C (-4 ... 185 °F)
Cable, fixed installation		-40 ... 80 °C (-40 ... 176 °F)
Cable, flexing		-5 ... 80 °C (23 ... 176 °F)
Pollution degree		3
Mechanical specifications		
Plug connector		
Tightening torque		0.6 Nm
Tool installation		screw M2.5 x 27.5
Mating cycles		min. 100
Degree of protection		IP65 / IP67
Cable		according to IEC/EN 60228 (DIN VDE 0295) class 5
Sheath diameter		4.8 mm
Bending radius		> 10 x cable diameter, movable installation > 5 x cable diameter, fixed installation
Sheath color		black (similar to RAL 9005)
Number of cores		3
Core cross section		0.5 mm^2
Cores color		Core 1: black 1 Core 2: black 2 Core PE: green/yellow
Core construction		16 x 0.2 mm Ø
Length	L	2 m
Cable code		Li YY 3 x 0,50
Mass		158 g
Material		
Plug connector		
Body		TPU, black
Seal		TPU , molded
Contact surface		Sn
Flammability		V-0
Cable		
Sheathing		PVC
Cores		bare copper (Cu)
Core insulation		PVC
Oil resistance		good
Flammability		V-0

Connection





Release date: 2025-02-04 Date of issue: 2025-02-04 Filename: 247580_eng.pdf