




## Actuator Flap (Ex e)

### CFP.ZB.SP

- Protective flap for small actuator heads
- Ex e certified
- Polycarbonate
- Component for appropriately certified Ex e enclosures

Small actuator protective flap for use with small actuators, cover-mounted with type of protection Ex e

## Dimensions



Dimension values see data table.

Image and drawing are generic for this device type and may deviate from the specific variant.

## Technical Data

### Electrical specifications

|          |                                                    |
|----------|----------------------------------------------------|
| Function | Small actuator head protective flap, cover-mounted |
| Color    | clear                                              |

### Mechanical specifications

|                        |                                        |
|------------------------|----------------------------------------|
| Degree of protection   | IP66                                   |
| Material               | Polycarbonate                          |
| Mass                   | 54 g                                   |
| Dimensions             |                                        |
| External dimension (A) | 72 mm                                  |
| External dimension (B) | 44 mm                                  |
| External dimension (C) | 37 mm                                  |
| Mounting               | use with cover-mounted contact modules |

### Ambient conditions

|                     |                                |
|---------------------|--------------------------------|
| Ambient temperature | -40 ... 55 °C (-40 ... 131 °F) |
|---------------------|--------------------------------|

### Data for application in connection with hazardous areas

|                                 |                                           |
|---------------------------------|-------------------------------------------|
| EU-type examination certificate | CML 16 ATEX 3339U                         |
| Marking                         | Ⓔ II 2 GD<br>Ex e IIC Gb<br>Ex tb IIIC Db |

### International approvals

|                |                    |
|----------------|--------------------|
| IECEx approval | IECEx CML 16.0114U |
|----------------|--------------------|

Release date: 2026-04-07 Date of issue: 2026-04-07 Filename: 290165\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

**PEPPERL+FUCHS**

Technical Data

| General information       |                    |                                                    |
|---------------------------|--------------------|----------------------------------------------------|
| Supplementary information |                    | For more information please contact Pepperl+Fuchs. |
| Enclosure type            | LR* SR*.CS* GR.CS* |                                                    |

Release date: 2026-04-07 Date of issue: 2026-04-07 Filename: 290165\_eng.pdf