



13,56 MHz HF RFID Reader (CSL)

Ident-Ex 01 NH CSL Wacker - 13,56MHz HF RFID



- Ultra-rugged
- Outstanding head modules performances
- Easy to use, with one hand
- Flexibility - online / offline scanning & changeable head modules
- Pairable with any Bluetooth device
- Ideal for intensive and challenging data collection
- Lower cost - prevents legacy tag replacement
- Ideal for intensive scanning and 12 hour shifts

Intrinsically safe Bluetooth® handheld for HF RFID (CSL)



Technical Data

General specifications

Description	HF RFID Reader Module CSL
Operating frequency	13.56 MHz HF

Hardware

Internal data memory	2 MByte
----------------------	---------

Electrical specifications

Battery type	Li-Ion battery Rechargeable 10.000+ scans with one battery charge
Operating duration	approx. 12 h

Communication

Bluetooth	Class II, up to approx. 10 meters
-----------	-----------------------------------

Standard conformity

RFID	ISO/IEC 15693 ISO/IEC 14443 ISO/IEC 18000-3 (I-CODE ; NTAG ; my D™ Infineon)
------	--

Software

Applications	eSETUP Ident-Ex®, eSETTINGS Ident-Ex® (API DEMO)
--------------	--

Mechanical specifications

Degree of protection	IP64
Mass	499 g
Dimensions	221 mm x 84 mm x 58 mm


Data for application in connection with hazardous areas

ATEX approval	
ATEX marking	⊕ II 2D Ex ib IIIC T135°C Db IP6X ⊕ II 2G Ex ib IIC T4 Gb IP64

International approvals

IECEx approval	
IECEx marking	Ex ib IIC T4 Gb IP64 Ex ib IIIC T135°C Db IP 6X
ETL approval	Class I, II, III, Division 1 Groups A-G, T4, T 135°C Cl I Zn 1, AEx ia IIC T4 Gb IP64

Accessories

	SCANNER-HOLDER-U1-XX00-N0	Stainless steel holder for for IDM-Z1- handheld readers, compatible with AG-XX00 housing
---	----------------------------------	--

Release date: 2020-12-10 Date of issue: 2020-12-10 Filename: 320519_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com







Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com



13,56 MHz HF RFID Reader (CSL)

Accessories

	SCANNER-HOLDER-U1-AG1-N0	Stainless steel holder for for IDM-Z1- handheld readers, compatible with AG1 housing
	Wrist strap	Hand strap
	LC RL01	Leather Case for Retractable Lanyard
	LH ID01	Leather holster
	RL ID01	Retractable Lanyard
	DC ID01	Docking station

Release date: 2020-12-10 Date of issue: 2020-12-10 Filename: 320519_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**