



Tablet computer



Tab-Ex02-DZ1-WWANEUR-ANDCS00..

- Replaceable SIM
- Wireless connections such as WWAN, 4G LTE, WLAN, etc.
- Camera (front and main/optional)
- 8 MP camera with built-in flash on the main screen
- 5 MP front camera
- Comprehensive security thanks to Samsung KNOX
- Accessories and peripheral devices allow a wider range of applications
- Suitable for use with gloves
- NFC technology for wireless applications
- GPS
- Global certificates - a common platform
- Latest available Android version for this device

Tab-Ex 02 DZ1 (DIV 1 & Zone 1/21), latest available Android firmware release, WWAN (LTE) incl. WiFi, with camera, with microSD card, version for Europe



Technical Data

Hardware

Processor	Exynos 7 Octa, 1.6 GHz Octa-core (Cortex®-A53)
Working memory	RAM 3 GByte
Camera	
Front camera	5 MP
Main camera	8 MP Autofocus
Video recording resolution	Full HD (1920 x 1080 pixels) @ 30 fps
Optional data memory	Micro SD flash card up to 256 GByte
Internal data memory	16 GByte
Sensors	Acceleration sensor, proximity and ambient light sensor, gyroscope, geomagnetic, Hall sensor, facial recognition

Indicators/operating means

Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	20.31 cm
Resolution	1280 x 800 (WXGA)
Brightness	480 nit
Colors	16 Mio.

Electrical specifications

Battery type	Li-Ion battery 16.91 WH 3.8 V 4450 mAh
Operating duration	up to 11 h

Communication

Mobile standard	LTE Cat. 6 (300 Mbps)
2G	GSM 850 MHz, GSM 900 MHz, DCS 1800 MHz, PCS 1900 MHz
3G	UMTS band: B1 (2100), B2 (1900), B4 (AWS), B5 (850), B8 (900)
4G	LTE band: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B7 (2600), B8 (900), B17 (700), B20 (800), B28 (700)
WLAN	802.11 a/b/g/n/ac (2.4 GHz + 5 GHz)
Bluetooth	Bluetooth® 4.2

Release date: 2020-12-09 Date of issue: 2020-12-09 Filename: 480982-100185_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com






Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

GPS sensor	GPS, Glonass, Beidou
USB	USB 2.0
Connections	Wi-Fi Direct, NFC, ANT+
SIM card	1 x Nano SIM (4FF)
Software	
Operating system	Android™
Languages	Deutsch English (default)
Safety	Samsung KNOX 3.2
SMS/MMS	yes
Ambient conditions	
Ambient temperature	-20 ... 50 °C (-4 ... 122 °F)
Mechanical specifications	
Degree of protection	IP64
Mass	1250 g
Dimensions	H x W x D 162 mm x 256 mm x 33.3 mm
Data for application in connection with hazardous areas	
ATEX approval	
ATEX certificate	SIRA 19 ATEX 1017 X
ATEX marking	Ⓜ II 2G Ex db ia op is IIC T5 Gb Ⓜ II 2D tb ia op is IIIC T100 °C Db
International approvals	
CSA approval	
CSA certificate	19.80012318X
Approved for	Class I, II, Division 1, Groups A-G T5 Class I, Zone 1, AEx db ia op is IIC T5 Gb Zone 21 AEx tb ia op is IIIC T100°C Db
IECEX approval	
IECEX certificate	IECEX SIR 19.0012X
IECEX marking	Ex db ia op is IIC T5 Gb Ex tb ia op is IIIC T100 °C Db
Approved for	Europe
General information	
Scope of delivery	Tab-Ex® 02 Battery Stylus holder S Pen Safety Box USB cable Travel charger Documentation Micro SD flash card

Accessories



















	TC T02 (UK) TRAVEL CHARGER	Travel charger
	LC T01 X1	Leather bag
	CH T01 X1	Chest strap carrying system
	Carrying Strap (cushioned)	Carrying strap (padded) for leather bags
	PC T01	USB connection cable

Release date: 2020-12-09 Date of issue: 2020-12-09 Filename: 480982-100185_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.comUSA: +1 330 486 0002
pa-info@us.pepperl-fuchs.comGermany: +49 621 776 2222
pa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com
 **PEPPERL+FUCHS**

Accessories

	DS T01 X1 (EU)	Docking station
	DS T01 X1 (UK)	Docking station
	VH T01 X1e Vehicle Holder (passiv) Non-Ex	Vehicle mount
	CC S01-R	Car charger
	ST T02 X2 S Pen	S Pen
	S Pen Tips u. Tweezers	Tip ends and tip removal tweezers for ST T02 X2
	LC T01 X2	Leather case for Tab-Ex® 01 and 02 D2/Z2/DZ2
	CH T01 X2	Chest strap carrying system
	SB T01 Safety Box für Tab-Ex 01 / 02 DZ1	Safety Box
	DS T01 X1 (US)	Docking station
	DS T01 X1 (AU)	Docking station
	PSA1uB1E-E	Micro-USB to Ethernet Adapter
	Tether ST 01 Stylus	Stylus tether
	TC T02 (EU) Travel Adapter	Travel charger
	TC T02 (US) Travel Adapter	Travel charger
	TC T02 (AU) Travel Adapter	Travel charger
	BC T01	Belt loop with carabiner
	Samsung EVO PLUS microSDXC	256 GB microSD card for Tab-Ex® 02