



# Smartphone



## Smart-Ex02-ROW-DZ1ARE-ANDC00..

- Replaceable SIM
- Global certificates - a common hardware platform
- Android™ 9 operating system
- Upgrade to Android™ 11 now available.
- Wireless connections such as WWAN, 4G LTE, WLAN, etc.
- Android™ Enterprise Recommended verified device
- GPS
- NFC technology for wireless applications
- Service contract
- Special buttons for lone worker protection (LWP) applications
- Programmable hardware buttons

Smart-Ex 02 DZ1 (DIV 1 & Zone 1/21), latest available Android firmware release, with camera, version for United Arab Emirates and Saudi Arabia



### Technical Data

#### Hardware

Processor	Qualcomm Snapdragon 450
Working memory	RAM 3 GByte
Camera	
Front camera	5 MP
Main camera	12 MP with autofocus and LED flash
Video recording resolution	1080p HD, 720p HD, 480p (main camera)
Optional data memory	Micro SD flash card up to 128 GByte
Internal data memory	32 GByte
Speaker	Forward facing main speaker with Gore® cone
Microphone	Dual-mic solution with three selectable background noise suppression options

#### Indicators/operating means

Display	Can be operated while wearing gloves Extreme shock and scratch resistant Gorilla® glass
Touchscreen technology	Capacitive multitouch
Screen diagonal	12.7 cm
Resolution	720 x 1280 pixels
Key	PTT / Alarm / Power / Multifunction / Volume / Hardware buttons for Android features

#### Electrical specifications

Battery type	Li-Ion battery 16.28 WH 3.7 V 4400 mAh
Operating duration	LTE standby time: up to 350 h

#### Communication

Mobile standard	
2G	GSM: 850 MHz, 900 MHz, 1800 MHz, 1900 MHz
3G	UMTS: 850 MHz, 900 MHz, 1700 MHz, 1900 MHz, 2100 MHz
4G	LTE FDD: B1, B2, B3, B4, B5, B7, B8, B11, B12, B13, B20, B21, B25, B26, B28, B66, B71 LTE TDD: B38, B39, B40, B41
WLAN	802.11 a/b/g/n/ac/e/k/r/h (2,4 GHz + 5 GHz)
Bluetooth	Bluetooth® 4.2
GPS sensor	GPS, A-GPS, Glonass, Beidou, Galileo
NFC	yes

Release date: 2021-07-12 Date of issue: 2021-07-12 Filename: 480986-100047\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com






Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com



## Technical Data

SIM card	Dual Nano-SIM
<b>Software</b>	
Operating system	Android™ 9 Android™ Enterprise Recommended verified device Upgrade to Android™ 11 now available.
SMS/MMS	yes
<b>Ambient conditions</b>	
Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
<b>Mechanical specifications</b>	
Degree of protection	IP68 , MIL-STD-810G
Connection	Waterproof magnetic USB 2.0 port 3.5 mm jack connection with special ecom mounting solution
Mass	approx. 380 g
Dimensions	H x W x D 163 mm x 82 mm x 22 mm
<b>Data for application in connection with hazardous areas</b>	
ATEX approval	
ATEX certificate	EPS 19 ATEX 1 068 X
ATEX marking	Ⓜ II 2G Ex ib op is IIC T4 Gb IP64 Ⓜ II 2D Ex ib op is IIIC T120°C Db Ta = -20 °C to +60 °C
<b>International approvals</b>	
SGS approval	
SGS certificate	CI I, II, III, Division 1 Group A-G T4 IP 64 Ex ib op is IIC T4 Gb Ex ib op is IIIC T120°C C Db CI 1 Zn 1, AEx ib op is IIC T4 Gb Zn 21, AEx ib op is IIIC T120°C Db Ta = -20 °C to +60 °C, IP 64
IECEX approval	
IECEX certificate	IECEX EPS 19.0031X
IECEX marking	Ex ib op is IIC T4 Gb IP64 Ex ib op is IIIC T120°C Db Ta = -20 °C to +60 °C
Approved for	United Arab Emirates , Saudi Arabia
<b>General information</b>	
Note	Android is a trademark of Google LLC.
Scope of delivery	Smart-Ex® 02 Li-Ion battery Charger USB cable Screwdriver Documentation

## Accessories

	<b>RL ID01</b>	Retractable Lanyard
	<b>MINI QD LOOP</b>	Mini QD Loop
	<b>EXT-C2LCOIL CLIP2LOOP COIL</b>	Clip2Loop Coil Tether
	<b>BC-Ex</b>	Belt clip with QuickFix
	<b>DS S02</b>	Docking station

Release date: 2021-07-12 Date of issue: 2021-07-12 Filename: 480986-100047\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group  
www.pepperl-fuchs.com













 USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

 Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

 Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

## Accessories

	<b>TORX T8 SCREWDRIVER</b>	Torx screwdriver for Smart-Ex® 02 &Ex-Handy 10
	<b>LH S02</b>	Leather holster
	<b>TC S02 Travel Charger</b>	Travel charger
	<b>SUCTION CUP HOLDER</b>	Suction cup holder for Smart-Ex 02 &Ex-Handy 10
	<b>CR-EX S02</b>	Cradle for Smart-Ex® 02
	<b>LC S02</b>	Leather case for Smart-Ex® 02
	<b>CC S01-R</b>	Car charger
	<b>DC EX-BP S02</b>	Battery pack charger for Ex-BP S02 &BP S02
	<b>Ex-BP S02</b>	Battery pack
	<b>ST 01</b>	Stylus pen
	<b>Tether ST 01 Stylus</b>	Stylus tether
	<b>PC S02</b>	USB Charging Cable for Smart-Ex 02 and Ex-Handy 10