



Tablet computer

Tab-Ex® 03 DZ1

TAB-EX03-DZ1-WIFINAM-CS-000-..



- NFC technology for wireless applications
- Comprehensive security thanks to Samsung KNOX
- Suitable for use with gloves
- Google ARCore
- Samsung DeX Mode
- MIL-STD-810H
- 64 GB internal memory
- Micro SD slot, 512 GB
- 13 MP rear camera + 5 MP front camera

Tab-Ex 03 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, WiFi, with camera, with microSD card, version for Northern America



Technical Data

Hardware

Processor	Octa-core, 4 x 2.7 GHz + 4 x 1.7 GHz Exynos 9810
RAM	4 GB
Camera	
Front camera	5 MP
Main camera	13 MP Autofocus
Video recording resolution	UHD 4K (3840 x 2160 Pixel) @ 30 fps
Internal data memory	64 GByte Free available memory 48.6 GByte
Optional data memory	microSD (up to 1024 GB) 512 GB installed
Sensors	Acceleration sensor, ambient light sensor, gyroscope, geomagnetic sensor, Hall sensor,
Speaker	yes

Indicators/operating means

Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	20.31 cm
Aspect ratio	16:10
Resolution	1920 x 1200 (WUXGA)
Brightness	480 cd/m ² (nit)
Colors	16 Mio.

Electrical specifications

Battery type	Li-Ion 18.87 WH, 3.8 V 5050 mAh (typical) 4900 mAh (rated)
Operating duration	up to 11 h

Communication

Mobile standard	
WLAN	802.11 a/b/g/n/AC/ax 2.4 G+5 GHz, HE80, MIMO, 1024 QAM
Bluetooth	Bluetooth® 5.0
GPS sensor	GPS, Glonass, Beidou, Galileo

Release date: 2024-04-05 Date of issue: 2024-04-05 Filename: 480989-100022_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com



Technical Data

USB	USB 3.1 Gen. 1
Connections	Wi-Fi Direct, NFC, ANT+
Software	
Operating system	Android™ 13
Safety	Samsung KNOX 3.x
Ambient conditions	
Ambient temperature	-20 ... 50 °C (-4 ... 122 °F)
Mechanical specifications	
Degree of protection	IP64 according to EN/IEC 60079-0 (ATEX/IECEX)
Mass	1100 g
Dimensions	
W x H x D	161.5 mm x 262.75 mm x 25.75 mm
International approvals	
IECEX approval	
IECEX certificate	IECEX EPS 22.0014X
IECEX marking	Ex db ia IIC T6 Gb Ex ia tb IIIC T80°C Db
ETL approval	5027822
Approved for	Class I, Division 1, Groups A, B, C, D, T6 Class I, Zone 1, AEx db ia IIC T6 Gb Ex db ia IIC T6 Gb
Approved for	Northern America
Further approvals	MIL-STD-810H
General information	
Scope of delivery	Tab-Ex® 03 S Pen USB cable Charger Documentation Micro SD flash card

Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.