



# Smartphone



## Smart-Ex02-ROW-DZ1KOR-ANDC00..

- Replaceable SIM
- Global certificates - a common hardware platform
- Wireless connections such as WWAN, 4G LTE, WLAN and Bluetooth®
- Android™ Enterprise Recommended verified device
- GPS
- NFC technology for wireless applications
- Service contract
- Special buttons for lone worker protection (LWP) applications
- Programmable hardware buttons
- Android™ 11 operating system

Smart-Ex 02 DZ1 (DIV 1 and Zone 1/21), latest available Android firmware release, with camera, version for South Korea



### Technical Data

<b>Hardware</b>	
Processor	Qualcomm Snapdragon 450
RAM	3 GByte
<b>Camera</b>	
Front camera	5 MP
Main camera	12 MP with autofocus and LED flash
Video recording resolution	1080p, 720p, 480p (main camera)
Optional data memory	Micro SD flash card up to 128 GByte
Internal data memory	32 GByte
Speaker	Forward facing main speaker with Gore® cone
Microphone	Dual-mic solution with three selectable background noise suppression options
<b>Indicators/operating means</b>	
Display	Extreme shock and scratch resistant Gorilla® Glass with glove touch and wet mode
Touchscreen technology	Capacitive multitouch
Screen diagonal	12.7 cm
Resolution	720 x 1280 pixels
Key	PTT / Alarm / Power / Multifunction / Volume / Hardware buttons for Android features
<b>Electrical specifications</b>	
Battery type	Li-Ion battery 16.28 WH 3.7 V 4400 mAh
Operating duration	LTE standby time: up to 350 h
<b>Communication</b>	
<b>Mobile standard</b>	
2G	GSM: 850 MHz, 900 MHz, 1800 MHz, 1900 MHz
3G	UMTS: 850 MHz, 900 MHz, 1700 MHz, 1900 MHz, 2100 MHz
4G	LTE FDD: B1, B2, B3, B4, B5, B7, B8, B11, B12, B13, B20, B21, B25, B26, B28, B66, B71 LTE TDD: B38, B39, B40, B41
WLAN	802.11 a/b/g/n/ac/e/k/r/h (2,4 GHz + 5 GHz)
Bluetooth	Bluetooth® 4.2
GPS sensor	GPS, A-GPS, Glonass, Beidou, Galileo
NFC	yes
SIM card	Dual Nano-SIM








Release date: 2022-06-01 Date of issue: 2022-06-01 Filename: 480986-100060\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

Software	
Operating system	Android™ 11 Android™ Enterprise Recommended verified device
SMS/MMS	yes
Ambient conditions	
Ambient temperature	-20 ... 60 °C (-4 ... 140 °F)
Mechanical specifications	
Degree of protection	IP68 , MIL-STD-810G
Connection	7-pins water-proof magnetic USB 2.0 port 3.5 mm jack connection with special ecom mounting solution
Mass	approx. 380 g
Dimensions	
W x H x D	82 mm x 163 mm x 22 mm
Data for application in connection with hazardous areas	
ATEX approval	
ATEX certificate	EPS 19 ATEX 1 068 X
ATEX marking	Ⓜ II 2G Ex ib op is IIC T4 Gb IP64 Ⓜ II 2D Ex ib op is IIC T120°C Db Ta = -20 °C to +60 °C
International approvals	
IECEX approval	
IECEX certificate	IECEX EPS 19.0031X
IECEX marking	Ex ib op is IIC T4 Gb IP64 Ex ib op is IIC T120°C Db Ta = -20 °C to +60 °C
KCC approval	
KCC marking	Ex ib op is IIC T4 Ex ib op is IIC T120°C
Approved for	South Korea
General information	
Note	Android is a trademark of Google LLC.
Scope of delivery	Smart-Ex® 02 Li-Ion battery Charger USB cable Screwdriver Documentation

## Accessories

	<b>EXT-C2LCOIL</b>	Clip2Loop coil tether
	<b>RL ID01</b>	Retractable lanyard
	<b>SUCTION CUP HOLDER</b>	Suction cup holder for Smart-Ex 02 and Ex-Handy 10
	<b>LH S02</b>	Leather holster
	<b>MINI QD LOOP</b>	Mini QD loop
	<b>TC S02 Travel Charger (EU/UK/US/AU)</b>	Travel charger
	<b>CR-EX S02</b>	Cradle for Smart-Ex® 02

Release date: 2022-06-01 Date of issue: 2022-06-01 Filename: 480986-100060\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com












USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

## Accessories

	<b>TORX T8 SCREWDRIVER</b>	Torx screwdriver for Smart-Ex® 02 and Ex-Handy 10
	<b>BC-Ex</b>	Belt clip with QuickFix
	<b>DS S02</b>	Docking station
	<b>LC S02</b>	Leather case for Smart-Ex® 02
	<b>CC S01-R</b>	Car charger
	<b>DC EX-BP S02</b>	Battery pack charger for Ex-BP S02 & BP S02
	<b>Ex-BP S02</b>	Battery pack
	<b>ST 01</b>	Stylus pen
	<b>Tether ST 01 Stylus</b>	Stylus tether
	<b>PC S02</b>	USB Charging Cable for Smart-Ex 02, Ex-Handy 10 and Pocket Unit PU-Ex V01
	<b>SC-Ex</b>	Spring clip with 4QuickFix