



VisuNet RM Shell PRO License Key

VISUNET-RM-SHELL4-PRO

- Restricted Web browser (Internet Explorer-based): Allows the secure direct access of HTML-based MES and SCADA systems
- Restricted Web browser (Chrome-Engine-based): HTML5 compatible web browser that enables the secure access of websites and web-applications.
- Desktop Sharing: Clone a Remote Monitor to work with one host system from several Remote Monitors simultaneously (RM Shell 4.0.3)
- Citrix Receiver: Directly access Citrix XenApp/XenDesktop infrastructures from the Remote Monitor (RM Shell 4.0.3)
- Raritan KVM Profile: Client allows to directly connect to Raritan Dominion KX II-101 V2 KVM-Switch

Function

Pepperl+Fuchs VisuNet Remote Monitors (VisuNet RM) are industrial grade Thin Client solutions that provide a simplified, modern user interface to the operators. The firmware of a VisuNet RM, called VisuNet RM Shell, enables the users to easily access the applications that run on a process control systems via Ethernet.

With the RM Shell 4.0 Pro license key, additional features can be enabled in the RM Shell 4.0

Please refer to the feature matrix to see which features are unlocked in which RM Shell 4.x version with the PRO license key.

Technical Data

Software

Operating system	based on Microsoft Windows Embedded Standard 7
Languages	English
Licensing	
Available licenses	1x license key to enable "Pro" features of one VisuNet Remote Monitor with pre-installed RM Shell 4.x
Installation	Licenses can only be enabled in the RM Shell 4.x by user role "Administrator".
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 4.x

Release date: 2023-12-11 Date of issue: 2023-12-11 Filename: 547745_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

License Bundles

Product	Number of Licenses	Part Number
VISUNET-RM-SHELL4-PRO-5	5	548005
VISUNET-RM-SHELL4-PRO-10	10	548006
VISUNET-RM-SHELL4-PRO-30	30	548007

Features unlocked with PRO License (#547745)

Features	RM Shell 4.0.1	RM Shell 4.0.2	RM Shell 4.0.3	RM Shell 4.1.0	Description
Restricted web browser, based on Internet Explorer	x	x	x	x	Fast HTML browser that uses Internet Explorer for rendering websites. Operators can be restricted to only visit specified websites.
Restricted web browser, based on Chrome engine	-	-	x	x	Fast HTML5 browser that uses the Google Chrome rendering engine. Operators can be restricted to only visit specified websites.
Citrix Receiver 4.4	-	-	x	x	Latest version of Citrix Receiver client, compatible with Citrix XenApp & XenDesktop.
Desktop sharing	-	-	x	x	This feature allows to clone a Remote Monitor and display its desktop on other VisuNet Remote Monitors (requires RM Shell 4.0.3 or later)
Raritan KVM profile	-	-	-	x	Client allows to directly connect to Raritan Dominion KX II-101 V2 KVM-Switch

Release date: 2023-12-11 Date of issue: 2023-12-11 Filename: 547745_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".