


Thin Client Firmware VisuNet Control Center 6



- User-friendly, centralized management tool
- Remotely configure (e.g., IP address) Remote Monitors
- Create and edit remote profiles (e.g. a RDP connection profile) on a Remote Monitor
- Copy profiles from one Remote Monitor to another Remote Monitor
- Monitor the operators screen and support them remotely via "session shadowing"

Additional Management tool for VisuNet Remote Monitors and Box Thin Clients

Function

The VisuNet Control Center (VisuNet CC) is a software tool for the centralized management of Pepperl+Fuchs VisuNet Remote Monitors. The software can be installed on any Windows-based PC (e.g. a PC in the control room). This allows remotely setup, managing and maintaining all Remote Monitors that are connected to the same network infrastructure.

Technical Data

Software

Operating system	Requires Microsoft Windows operating system and Microsoft .NET Framework v. 4.7.2. or RM Shell 6. Compatible with Pepperl+Fuchs Remote Monitors with RM Shell 5 and 6.
Languages	English
Licensing	Requires VisuNet Control Center License entered on every Pepperl+Fuchs Remote Monitor that should be managed with the Control Center
Available licenses	CC license key
Installation	Download installer and install Software on any Windows-based Desktop PC that is connected to the same network as the VisuNet Remote Monitors
Associated products	VisuNet Remote Monitors with pre-installed RM Shell 6 See the table below for available licenses.

Release date: 2024-01-04 Date of issue: 2024-01-04 Filename: 70168431_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Product Versions

Shell 6 CC

Part No.	Model Number
XSP2-037-01R	VISUNET-RM-SHELL6-CC-DLK
70162159	VISUNET-RM-SHELL6-CC
70162160	VISUNET-RM-SHELL6-CC-5
70162161	VISUNET-RM-SHELL6-CC-10
70162162	VISUNET-RM-SHELL6-CC-30
70162164	VISUNET-RM-SHELL6-CC-50

Release date: 2024-01-04 Date of issue: 2024-01-04 Filename: 70168431_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**