

# Zener Barrier

## Z961

- 2-channel
- AC version
- Working voltage 6.5 V at 10 µA
- Series resistance max. 106  $\Omega$
- Fuse rating 100 mA
- DIN rail mountable














#### **Function**


The Zener Barrier prevents the transfer of unacceptably high energy from the safe area into the hazardous area. The zener diodes in the Zener Barrier are connected in the reverse direction. The breakdown voltage of the diodes is not exceeded in normal operation. If this voltage is exceeded, due to a fault in the safe area, the diodes start to conduct, causing the fuse to blow. The Zener Barrier has alternating polarities, i. e. interconnected zener diodes are employed and one side is grounded. The Zener Barrier can be used for both alternating

voltage signals and direct voltage signals.

Depending on the application, increased or decreased intrinsic safety parameters apply for serial or parallel connection. For the detailed parameters refer to the Zener Barrier certificate. Application examples can be found in the system description of the Zener Barriers.

### Connection





Zone 2 Div. 2

#### **Technical Data**

General specifications	
Туре	AC version
Electrical specifications	
Nominal resistance	100 Ω
Series resistance	max. 106 Ω
Fuse rating	100 mA
Hazardous area connection	
Connection	terminals 1, 2; 3, 4
Safe area connection	
Connection	terminals 5, 6; 7, 8


Release date: 2023-04-06 Date of issue: 2023-04-06 Filename: 071795\_eng.pdf

#### Technical Data Working voltage Supply loop max. 7.7 V Measurement loop max. 6.5 V at 10 μA Conformity Degree of protection IEC 60529 **Ambient conditions** Ambient temperature -20 ... 60 °C (-4 ... 140 °F) Storage temperature -25 ... 70 °C (-13 ... 158 °F) Relative humidity max. 75 %, without condensation **Mechanical specifications** Degree of protection IP20 Connection screw terminals max. 2 x 2.5 ... mm<sup>2</sup> Core cross section Mass approx. 150 g **Dimensions** 12.5 x 115 x 116 mm (0.5 x 4.5 x 4.6 inch) (W x H x D) modular terminal housing, see system description Construction type on 35 mm DIN mounting rail acc. to EN 60715:2001 Mounting Data for application in connection with hazardous areas EU-type examination certificate **BAS 01 ATEX 7005** Marking Voltage $U_{\circ}$ 8.7 V Current $I_{o}$ 89 mA Power $P_0$ 190 mW Supply 250 V Maximum safe voltage $U_{\mathsf{m}}$ Series resistance min. 98 Ω TÜV 99 ATEX 1484 X Certificate Marking Directive conformity EN IEC 60079-0:2018+AC:2020, EN 60079-11:2012, EN 60079-15:2010 Directive 2014/34/EU International approvals FM approval Control drawing 116-0118 **UL** approval Control drawing 116-0139 (cULus) IECEx approval IECEx BAS 09.0142 IECEx BAS 17.0091X IECEx certificate [Ex ia Ga] IIC , [Ex ia Da] IIIC , [Ex ia Ma] I Ex ec IIC T4 Gc **IECEx** marking **General information** Supplementary information Observe the certificates, declarations of conformity, instruction manuals, and manuals



where applicable. For information see www.pepperl-fuchs.com.

### **Assembly**



# **Matching System Components**

	ZH-ES/LB	Insertion Strip
.0.	ZH-Z.AB/NS	Mounting block for DIN mounting rail
***	ZH-Z.AB/SS	Mounting block for grounding rail
	ZH-Z.AK16	Connection terminal for grounding rail
	ZH-Z.AR.125	Spacing Roller
	ZH-Z.BT	Label Carrier
C.	ZH-Z.ES	Single Socket
4	ZH-Z.LL	Ground Rail Feed
	ZH-Z.NLS-Cu3/10	Grounding Rail
	USLKG5	Terminal block for equipotential bonding