

Retroreflective sensor RLK39-54-Z/31/40a/116



- Glare protected with polarization filter
- Visible red light
- Light-on/dark-on, switchable
- Timer function
- Degree of protection IP54

Retroreflective sensor for standard applications, polarization filter, detection range 7 m, red light, timer function, sensitivity adjuster, light/dark on, relay contact output, terminal compartment

Dimensions



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Technical Data

		0.5.4
Effective detection range		05m
Reflector distance		0.1 5 m
I hreshold detection range		6 m
Reference target		H50 reflector
Light source		LED red
Light type		modulated visible red light
Polarization filter		yes
Ambient light limit		IEC / EN 60947-5-2 , 10000 Lux
Functional safety related parameters		
MTTF _d		803 a
Mission Time (T_M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Function indicator		LED yellow: switching state LED red: pre-fault indication
Control elements		Sensing range adjuster, light-on/dark-on changeover switch
Control elements		switch for timer function
Electrical specifications		
Operating voltage	U _B	12 240 V DC 24 240 V AC (50 60 Hz)
Ripple		10 %
No-load supply current	I ₀	≤ 50 mA
Protection class		II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Caution! The protection class 2 is only valid when the terminal compartment is closed. output circuit has basic insulation to control circuit according to IEC/EN 61140
Power consumption	Po	≤ 3 VA
Time delay before availability	t _v	≤ 300 ms
Output	v	
Switching type		light/dark on
Signal output		1 relay output
Switching voltage		max. 240 V AC ; 150 V DC
Switching current		max. 3 A
Switching power		DC: max. 90 W AC: max. 750 VA
Switching frequency	f	≤ 25 Hz
Response time		≤ 20 ms
Timer function		On-/off-delay or pulse extension on choice
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
CCC approval		Certified by China Compulsory Certification (CCC)
Approvals		CE
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP54
Connection		terminal compartment PG9 . $\leq 0.75 \text{ mm}^2$
Material		
Housing		РВТ
Optical face		PMMA
Mass		approx. 110 g
Dimensions		
Height		64 mm

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Retroreflective sensor

RLK39-54-Z/31/40a/116

Technical Data		
Width	25 mm	
Depth	75 mm	
General information		
Scope of delivery	Mounting aid , Reflector	

Connection Assignment



Installation



Wire length L _A [mm]	Strip length L _B [mm]
30±2	5±1

Recommendations for cable installation:

1. Use flexible cable with a bending radius less than $5 ext{ x}$ outer diameter.

2. Use cable with an outer diameter of 6.2 ±0.2 mm with the provided gasket with an inner diameter of 7 mm.

3. Cut, strip, and crimp the cable according to the dimensions in the table above.

4. Ensure that the distance between cable gland and housing is approximately 2 mm. Do not screw in the cable gland fully.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Characteristic Curve

Characteristic response curve



8

6

Additional Information

4

System Description

2

A retroreflective sensor contains emitters and receivers integrated in a single housing. The emitted light is reflected back to the receiver by a reflector. When the light beam is interrupted by an object, the switching function is triggered.

16

Mounting

0.1

-

0

The sensors can be mounted directly with thru-holes or using the mounting bracket supplied.

10

12

14

Distance X [mm]

Ensure that the background is level to prevent the housing from becoming distorted when the fittings are tightened.

Secure the nuts and screws with spring disks to prevent the sensor from becoming misaligned.

Mount a suitable reflector opposite the light barrier. Roughly align the sensor (without an object) with the reflector. Next, adjust the sensor to the reflector by swiveling the sensor horizontally and vertically so that the yellow signal indicator lights up continuously. In the event of misalignment, the red signal indicator lights up.

Commissioning

Checking object detection: Follow the steps below to check that the sensor detects objects as required. Position the object in the beam path of the sensor. When the object is detected, the yellow signal indicator goes out. If the yellow signal indicator remains lit, reduce the sensitivity of the When the object disappears from the beam path of the sensor, the yellow signal indicator lights up again continuously.

Maintenance

Cleaning: If the transmission reception deteriorates, e.g., due to dirt or misalignment, and is lower than the functional reserve, the red signal indicator on the receiver lights up. Clean the optical interfaces of the sensor (e.g., lenses) at regular intervals. Maintenance: Check the mounting fittings and the electrical connections regularly.

Configuration

Light beam	1					ight pass
Timer Mode						ight block
One shot	0	T	T	T	T	ON
	Ľ					OFF
		Т	Т		Т	ON
1 2 3 4						— OFF
Off-delay		Т	Т		Т	ON
		│┘ ┝┵╍Ĺ			┝╼┥	OFF
				Т		- ON
1 2 3 4		┝┽╧┲				OFF
On-delay		 −− □		┝╤┥		ON
		T		1		OFF
					┝╼┥	- ON
1 2 3 4		Ť	Т		Т	OFF
Normal						ON
	10					_ OFF
						- ON
1 2 3 4						OFF

O Denotes Light - ON T= 0.1 10 sec.

Denotes Dark - ON

Refer to "General Notes Relating to Pepperl+Fuchs Product Information". Pepperl+Fuchs Group USA: +1 330 486 0001 General-fuchs com fa-info@us pepperl-fuchs com

Pepperl+Fuchs Group www.pepperl-fuchs.com

5