


# Ultrasonic sensor UC500-30GM-IUR2-V15

- Parameterization interface for the application-specific adjustment of the sensor setting via the service program ULTRA 3000
- Analog current and voltage output
- Synchronization options
- Adjustable acoustic power and sensitivity
- Temperature compensation

### Single head system



# **Dimensions**




# **Technical Data**

General specifications	
Sensing range	30 500 mm
Adjustment range	50 500 mm
Dead band	0 30 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 380 kHz
Response delay	21 ms minimum 63 ms factory setting
Indicators/operating means	
LED green	solid: Power-on flashing: Standby mode or program function object detected

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2022-12-13 Date of issue: 2022-12-13 Filename: 104092\_eng.pdf


Technical Data				
LED yellow 1		solid: object in evaluation range		
		flashing: program function		
LED yellow 2		solid: object in detection range flashing: program function		
LED red		solid: temperature/program plug not connected flashing: fault or program function object not detected		
Temperature/TEACH-IN connector		$\label{thm:compensation} Temperature\ compensation\ ,\ Evaluation\ range\ programming\ ,\ output\ function\ setting$		
Electrical specifications				
Operating voltage	U <sub>B</sub>	10 30 V DC , ripple 10 $\%_{\rm SS}$		
Power consumption	$P_0$	≤ 900 mW		
Time delay before availability	t <sub>v</sub>	≤ 500 ms		
Interface				
Interface type		RS 232, 9600 Bit/s , no parity, 8 data bits, 1 stop bit		
Input/Output				
Synchronization		bi-directional 0 level -U <sub>B</sub> +1 V 1 level: +4 V+U <sub>B</sub> input impedance: > 12 KOhm synchronization pulse: ≥ 100 µs, synchronization interpulse period: ≥ 2 ms		
Synchronization frequency				
Common mode operation		max. 95 Hz		
Multiplex operation		$\leq$ 95 Hz / n , n = number of sensors , n $\leq$ 5		
Output				
Output type		1 current output 4 20 mA 1 voltage output 0 10 V		
Resolution		evaluation range [mm]/4000, but ≥ 0.05 mm		
Deviation of the characteristic curve		≤ 0.2 % of full-scale value		
Repeat accuracy		≤ 0.1 % of full-scale value		
Load impedance		current output: ≤ 500 Ohm voltage output: ≥ 1000 Ohm		
Temperature influence		$\leq$ 2 % from full-scale value (with temperature compensation) $\leq$ 0.2 %/K (without temperature compensation)		
Compliance with standards and directives				
Standard conformity				
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 EN 60947-5-7:2003 IEC 60947-5-7:2003		
Approvals and certificates				
UL approval		cULus Listed, General Purpose		
CCC approval		CCC approval / marking not required for products rated ≤36 V		
Ambient conditions				
Ambient temperature		-25 70 °C (-13 158 °F)		
Storage temperature		-40 85 °C (-40 185 °F)		
Mechanical specifications				
Connection type		Connector plug M12 x 1 , 5-pin		
Housing diameter		30 mm		
Degree of protection		IP65		
Material				
Housing		stainless steel (1.4305 / AISI 303) PBT plastic parts		
Transducer		epoxy resin/hollow glass sphere mixture; polyurethane foam		
Mass		170 g		
Factory settings				
Output		evaluation limit A1: 60 mm evaluation limit A2: 500 mm rising ramp		



### **Connection**

#### Standard symbol/Connection:

(version IU)



Core colors in accordance with EN 60947-5-2.

# **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

### **Characteristic Curve**


### Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

**5**PEPPERL+FUCHS

# **Analogue output function**



### **Accessories**

	BF 30	Mounting flange, 30 mm
	BF 30-F	Plastic mounting adapter, 30 mm
900	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
0	M-105	Sensor well
	ULTRA3000	Software for ultrasonic sensors, comfort line
00	UVW90-M30	Ultrasonic -deflector
	UVW90-K30	Ultrasonic -deflector
000	M30K-VE	Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors
6/	V15-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
6/	V15-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 5-pin, PUR cable grey
10	UC-30GM-R2	Interface cable

#### Programming procedure

The sensor features 2 programmable analog outputs with programmable evaluation range. Programming the evaluation range and the operating mode is done either via the sensor's RS232 interface and ULTRA3000 software (see the ULTRA3000 software description) or by means of the programming plug at the sensor's back end which is described here.



Α2

Coded plug

E2/E3

#### **Programming of Evaluation Range**

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Place the target at the desired position for A1
- 5. Momentarily insert the programming plug in position A1 and then remove. This will program the position A1.
- 6. Place the target at the desired position for A2
- 7. Momentarily insert the programming plug in position A2 and then remove. This will program the position A2.

#### Notes:

- Removing the programming plug saves the new position into the device memory.
- The programming status is indicated by the LED. A flashing green LED indicates that the target is detected; a flashing red LED indicates that
  no target is detected.

#### **Programming the Operation Mode**

If the program mode is still activated, continue at number 4. If not, activate program mode by performing the sequence numbers 1 to 3.

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Insert the programming plug in position E2/E3. By removing and reinserting the plug, the user can toggle through the three different modes of operation. The selected mode is indicated by the LEDs as shown below:
  - Rising slope mode, LED A2 flashes
  - Falling slope mode, LED A1 flashes
  - · Zero line mode, LEDs A1 and A2 flash
- 5. Once the desired mode is selected, insert the programming plug in position T. This completes the programming procedure and saves the switch points and mode of operation.
- 6. The sensor now operates in normal mode.

#### Note:

The programming plug also functions as the temperature compensation. If the programming plug has not been inserted in the T position within 5 minutes, the sensor will return to normal operating mode with the latest saved values, without temperature compensation.

### **Factory Setting**


#### **Factory settings**

See technical data.

#### Indication

The sensor provides LEDs to indicate various conditions.

	Green LED	Red LED	Yellow LED A1	Yellow LED A2
During Normal Operation				
- Temperature compensated	On	Off	Object in evaluation	Object in sensing range
- with removed programming	Off	On	range	Object in sensing range
plug	Off	Flashing	Object in evaluation	remains in previous state
Interference (e.g. compressed		ū	range	·
air)		remains in previous state		
<b>During Sensor Programming</b>				
Evaluation limit A1:				
Object detected	Flashing	Off	Flashing	Off
No object detected	Off	Flashing	Flashing	Off
Evaluation limit A2:				
Object detected	Flashing	Off	Off	Flashing
No object detected	Off	Flashing	Off	Flashing
Operation mode:				
Rising slope mode	On	Off	Off	Flashing
Falling slope mode	On	Off	Flashing	Off
Zero line mode	On	Off	Flashing	Flashing
Standby	Flashing	Off	remains in previous state	remains in previous state



### **Commissioning**

#### **Synchronization**

This sensor features a synchronization input for suppressing ultrasonic mutual interference ("cross talk"). If this input is not connected, the sensor will operate using internally generated clock pulses. It can be synchronized by applying an external square wave. The pulse duration must be  $\geq$  100  $\mu$ s. Each falling edge of the synchronization pulse triggers transmission of a single ultrasonic pulse. If the synchronization signal remains low for  $\geq$  1 second, the sensor will revert to normal operating mode. Normal operating mode can also be activated by opening the signal connection to the synchronization input (see note below).

If the synchronization input goes to a high level for > 1 second, the sensor will switch to standby mode, indicated by the green LED. In this mode, the outputs will remain in the last valid output state.

#### Note:

If the option for synchronization is not used, the synchronization input has to be connected to ground (0 V) or the sensor must be operated via a V1 cordset (4-pin).

The synchronization function cannot be activated during programming mode and vice versa.

#### The following synchronization modes are possible:

- 1. Several sensors (max. number see technical data) can be synchronized together by interconnecting their respective synchronization inputs. In this case, each sensor alternately transmits ultrasonic pulses in a self multiplexing mode. No two sensors will transmit pulses at the same time (see note below).
- 2. Multiple sensors can be controlled by the same external synchronization signal. In this mode the sensors are triggered in parallel and are synchronized by a common external synchronization pulse.
- 3. A separate synchronization pulse can be sent to each individual sensor. In this mode the sensors operate in external multiplex mode (see note below).
- 4. A high level (+U<sub>B</sub>) on the synchronization input switches the sensor to standby mode.


#### Note

Sensor response times will increase proportionally to the number of sensors that are in the synchronization string. This is a result of the multiplexing of the ultrasonic transmit and receive signal and the resulting increase in the measurement cycle time.

### **Additional Information**

### Note on communication with the UC-30GM-R2 interface cable

The UC-30GM-R2 interface cable allows for communication with the ultrasonic sensor using ULTRA3000 software. The cable creates a connection between a PC RS-232 interface and the programming plug socket on the sensor. When connecting to the sensor, make certain the plug is lined up correctly; otherwise no communication will be possible. The key of the cable's plug must be aligned to the groove of the socket on the sensor (not with the arrow symbol on the sensor).



#### Programmable parameters with the ULTRA3000 software

- Evaluation limits A1 and A2
- Operation mode
- Sonic speed
- Temperature offset (The inherent temperature-rise of the sensor can be considered in the temperature compensation)
- Expansion of the unusable area (for suppression of unusable area echoes)
- Reduction of the detection range (for suppression of remote range echoes)

#### Ultrasonic sensor

- · Time of measuring cycle
- Acoustic power (interference of the burst duration)
- Sensitivity
- · Behavior of the sensor in case of echo loss
- · Behavior of the sensor in case of a fault
- · Average formation via an allowed number of measuring cycles
- Selection of the parameter set, RS 232 or manually

#### Note:

When connected to a PC and running the ULTRA3000 software, the sensor can act as a long term data logger as well.

### **Installation Conditions**

If the sensor is installed in an environment where the temperature can fall below 0 °C, one of these mounting flanges must be used for mounting: BF30, BF30-F, or BF 5-30.

If it is intended to operate the sensor at - 25 °C, we recommend discussing the mounting situation with a Pepperl + Fuchs application specialist to ensure a trouble-free operation.

If the sensor is mounted in a through hole using the included steel nuts, it must be mounted at the middle of the threaded housing. If it must be mounted at the front end of the threaded housing, plastic nuts with centering ring (optional accessories) must be used.