


# Ultrasonic sensor

- UB2000-F54-E4-V15
- Switching output
- 5 different output functions can be set
- Program input
- Synchronization options
- Deactivation option
- Temperature compensation

## Single head system



## **Dimensions**



Bore hole and countersinking for screws/hexagon M4




## **Technical Data**

Release date: 2022-12-01 Date of issue: 2022-12-01 Filename: 108161\_eng.pdf

General specifications	
Sensing range	80 2000 mm
Adjustment range	100 2000 mm
Dead band	0 80 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 175 kHz
Response delay	≤ 150 ms
Indicators/operating means	
LED green	solid green: monitoring system green flashing: program function

#### Technical Data LED yellow indication of the switching state flashing: program function object detected flashing: normal mode: error LED red Program function: no object detected permanently: Program mode, object uncertain **Electrical specifications** Operating voltage $U_{\mathsf{R}}$ 10 ... 30 V DC , ripple 10 $\%_{\text{SS}}$ No-load supply current $I_0$ Input/Output 1 synchronous input 0-level: -U<sub>B</sub>...+1 V 1-level: +4 V...+U<sub>B</sub> input impedance: > 12 KOhm Synchronization synchronization pulse: 0,1 ... 28 ms Synchronization frequency max. 33 Hz Common mode operation $\leq$ 33 / n Hz, n = number of sensors Multiplex operation 1 program input, switching point A1: -U<sub>B</sub> ... +1 V, switching point A2: +4 V ... +U<sub>B</sub> input impedance: > 4.7 k $\Omega$ , program pulse: $\geq$ 1 s Input type Output 1 switch output E4, NPN, NO/NC Output type Rated operating current 200 mA, short-circuit/overload protected $I_{e}$ Voltage drop $U^{q}$ Repeat accuracy ≤ 1 % of full-scale value max. 3 Hz Switching frequency f Range hysteresis Н ≤ 1 % of the set operating distance Temperature influence ± 1.5 % of full-scale value Compliance with standards and directives Standard conformity Standards EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 Approvals and certificates cULus Listed, Class 2 Power Source UL approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) Mechanical specifications Connection type Connector plug M12 x 1, 5-pin IP65 Degree of protection Material Housing ABS Transducer epoxy resin/hollow glass sphere mixture; polyurethane foam Mass 100 g



Ultrasonic sensor UB2000-F54-E4-V15

## **Connection**

Standard symbol/Connections:

(version E4, npn) (BN) 4 (BK) **5** + U<sub>B</sub> Switch output Program input (GY) Sync. input 3 (BU)

Wire colors in accordance with EN 60947-5-2.

## **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

ΒN (brown) 2 WH (white) BU (blue) 4 BK (black) GY (gray)

## **Characteristic Curve**


## Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

## **Characteristic Curve**

## Programmable output modes



5. A1 -> ∞, A2 -> ∞: Object presence detection mode Object detected: Switch output closed No object detected: Switch output open

## **Accessories**

21	UB-PROG2	Programming unit
6/	V15-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
6/	V15-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 5-pin, PUR cable grey

#### Additional Information

#### **Synchronisation**

The sensor features a synchronisation input for the suppression of mutual interference. If this input is not used, the sensor will operate using an internally generated clock rate. The synchronisation of multiple sensors can be realised as follows:

#### External synchronisation

The sensor can be synchronised by the external application of a square wave voltage. A synchronisation pulse at the synchronisation input starts a measuring cycle. The pulse must have a duration greater than  $100 \, \mu s$ . The measuring cycle starts with the falling edge of a synchronisation pulse. A low level  $> 1 \, s$  or an open synchronisation input will result in the normal operation of the sensor. A high level at the synchronisation input disables the sensor.

Two operating modes are available

- 1. Multiple sensors can be controlled by the same synchronisation signal. The sensors are synchronised.
- 2. The synchronisation pulses are sent cyclically to individual sensors. The sensors operate in multiplex mode.

#### Internal synchronisation

The synchronisation connections of up to 5 sensors capable of internal synchronisation are connected to one another. When power is applied, these sensors will operate in multiplex mode. The response delay increases according to the number of sensors to be synchronised. Synchronisation cannot be performed during TEACH-IN and vice versa. The sensors must be operated in an unsynchronised manner to teach the switching point.

#### Note:

If the option for synchronisation is not used, the synchronisation input has to be connected to ground (0V) or the sensor has to be operated via a V1 cable connector (4-pin).

#### Adjusting of switching points

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage  $-U_B$  or  $+U_B$  to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with  $-U_B$ , A2 with  $+U_B$ .

Five different output functions can be set

- 1. Window mode, normally-open function
- 2. Window mode, normally-closed function
- 3. One switching point, normally-open function
- 4. One switching point, normally-closed function
- 5. Detection of object presence

#### **TEACH-IN** window mode, normally-open function

- Set target to near switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>
- Set target to far switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>

#### **TEACH-IN** window mode, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>
- Set target to far switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>

#### **TEACH-IN** one switching point, normally-open function

- Set target to near switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -U<sub>B</sub>

#### TEACH-IN one switching point, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A2 with +U<sub>B</sub>

### **TEACH-IN** detection of object presence

- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -U<sub>B</sub>
- TEACH-IN switching point A2 with +U<sub>B</sub>

#### Default setting of switching points

A1 = unusable area

A2 = nominal sensing range



Displays in dependence on operating mode	Red LED	Yellow LED	Green LED
TEACH-IN switching point: Object detected No object detected Object uncertain (TEACH-IN invalid)	off flashes on	flashes off off	flashes flashes flashes
Normal operation	off	switching state	on
Fault	flashes	previous state	off