Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 115226_eng.pdf

Retroreflective sensor





- Robust photoelectric sensor series in a widely used standard housing
- Resistant against noise: reliable operation under all conditions
- Clear and functional display concept for the operating modes
- High level of stability thanks to the metal housing frame
- Tightly sealed thanks to welded plastic components
- Suitable for operation at low temperatures down to -40 °C

Robust retroreflective sensor for complex applications, small design, polarization filter, 9 m detection range, red light, light/dark on, PNP output, weak signal output, M12 plug










Dimensions




Technical Data **General specifications** 0 ... 6.5 m Effective detection range Reflector distance 0.01 ... 6.5 m Threshold detection range 9 m Reference target H85-2 reflector LED Light source Light type modulated visible red light, 660 nm Polarization filter Diameter of the light spot approx. 170 mm at detection range 6.5 m Opening angle 1.5° Ambient light limit 50000 Lux Continuous light 5000 Lux Modulated light Functional safety related parameters MTTF_d 1000 a Mission Time (T_M) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, flashes in case of short-circuit $2\ LEDs$ yellow, light up when light beam is free, flash when falling short of the stability control, off when light beam is interrupted Function indicator Control elements rotary switch for light/dark, sensitivity adjuster **Electrical specifications** U_B 10 ... 30 V DC Operating voltage Ripple max. 10 % No-load supply current I_0 max. 40 mA Output 1 PNP, inactive when level falls below function reserve after approx. 5 s. Immediately inactive if the beam is interrupted 4 times during the flashtime. Stability alarm output Switching type light/dark on switchable Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector max. 30 V DC Switching voltage Switching current max. 0.2 A Voltage drop $U_{\text{d}} \\$ ≤ 2.5 V DC Switching frequency f 1000 Hz Response time 0.5 ms Conformity Product standard EN 60947-5-2 Compliance with standards and directives Standard conformity Shock and impact resistance IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions Vibration resistance Approvals and certificates Protection class II, rated voltage ≤ 300 V AC with pollution degree 1-2 according to IEC 60664-1 **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -40 ... 60 °C (-40 ... 140 °F) Ambient temperature -40 ... 75 °C (-40 ... 167 °F) Storage temperature **Mechanical specifications** Housing width 41.5 mm Housing height 49 mm 15 mm Housing depth

Technical Data

Degree of protection	IP67
Connection	Metal connector, M12, 5-pin, 90° rotatable
Material	
Housing	Frame: nickel plated, die cast zinc, Laterals: glass-fiber reinforced plastic PC
Optical face	Plastic pane
Mass	60 g

Connection Assignment



- O = Light on
- = Dark on

Connection Assignment





Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

Assembly

Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 115226_eng.pdf





1	Operating display green	
2	Switch state	yellow
3	Light/dark switch	
4	Sensitivity adjuster	
5	Optical axis emitter	
6	Optical axis receive	er


Mounting


The sensors can be secured directly using thru-holes or using a mounting bracket or mounting clamp. Mounting brackets and clamping elements are available as accessories.

Ensure that the background is level to prevent the housing from becoming distorted when the fittings are tightened.

Secure the nut and screw with spring disks to prevent the sensor from becoming misaligned.

Characteristic Curve





System Description

System Description

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.

Commissioning

Aligning the sensor: Apply the operating voltage to the sensor. The operating indicator lights up green.

Mount a suitable reflector opposite the light barrier. Roughly align the sensor (without an object) with the reflector. Next, adjust the sensor to the reflector by swiveling the sensor horizontally and vertically so that the yellow signal indicator lights up continuously. In the event of misalignment, the yellow signal indicator flashes.

Commissioning
Checking object detection: Follow the steps below to check that the sensor detects objects as required.
Position the object in the beam path of the sensor.

When the object is detected, the yellow signal indicator goes out. If the yellow signal indicator remains lit, reduce the sensitivity of the potentiometer until the yellow signal indicator goes out.

When the object disappears from the beam path of the sensor, the yellow signal indicator lights up again continuously.

Maintenance

Maintenance

Cleaning: If the transmission reception deteriorates, e.g., due to dirt, the yellow signal indicator on the receiver flashes. Clean the optical interfaces of the sensor (e.g., lenses) at regular intervals.

Maintenance: Check the mounting fittings and the electrical connections regularly.

Accessories

Man	OMH-MLV12-HWG	Mounting bracket for series MLV12 sensors
	OMH-MLV12-HWK	Mounting bracket for series MLV12 sensors
12	OMH-K01	dove tail mounting clamp
1	OMH-K02	dove tail mounting clamp
~	OMH-K03	dove tail mounting clamp
	OMH-06	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm