Release date: 2022-12-15 Date of issue: 2022-12-15 Filename: 126087_eng.pdf

Control interface unit

IC-KP-B6-V15B

- Max. 4 read/write heads connectable
- Alternative 2 read/write heads and 2 trigger sensors can be connected
- LC display with background lightning
- Direct operation via 4 keys
- LED status indicator of bus communication and read/write heads

Control interface unit IDENTControl with PROFIBUS DP interface



Function

The innovative concept of the RFID identification system IDENTControl from Pepperl+ Fuchs has many advantages in comparison to other systems. The core piece of the system is the evaluation unit IDENTControl.

Thanks to the integrated interfaces for all standard field bus systems such as PROFIBUS, EtherNet, PROFINET IO, DeviceNet, serial connections (RS 232/RS 485/RS 422) and numerous connection options for inductive write/read heads as well as microwave antennas, the evaluation unit

IDENTControl can be adjusted to your needs in a flexible and easy manner.


LEDs indicate operating power and bus communication, connected write/read heads and active write/read commands.

Mounting the unit onto DIN mounting rails is easy thanks to the snap-fits on the back of the housing of the evaluation unit IDENTControl.

With its L-shaped housing, the evaluation unit including bus connector fits into a 120 mm grid in the switch cabinet. The mounting depth of 70 mm furthermore enables installation in flat switch boxes with a depth of only 100 mm.

There are 3 further mounting holes for field mounting.

Dimensions




Technical Data


General specifications

Technical Data Number of read/write heads alternative 2 read/write heads and 2 trigger sensors UL File Number E87056 Indicators/operating means LEDs 1, 2, 3, 4 Status indicator for read/write heads green: command at read/write head active yellow: approx. 1 second long, if command was successfully executed LED PWR/ERR green: power on red: Hardware fault LED UL green: Interface Power ON/OK LED Bus Error red: Bus error LED Data Exch green: Slave is at state "Data Exchange" LED DPV1 Yellow: not used LC display two-line multi-function display with 12 characters per line configuration of the control interface and display of connected read/write heads as additional pictograms; easy and direct selection of operating commands and addressing **Button** 4 keys: ESC, up, down and return Electrical specifications Ue 20 ... 30 V DC, PELV Rated operating voltage ≤ 10 % at 30 V DC Ripple Current consumption ≤ 2 A incl. read/write heads Power consumption P_0 3.5 W Without read/write heads basic insulation acc. to DIN EN 50178, rated insulation voltage of 50 V_{eff} Galvanic isolation Interface Physical RS-485 PROFIBUS DP acc. to EN 50170 Protocol Transfer rate 9.6: 19.2: 93.75: 187.5: 500: 1500 kBit/s 3; 6; 12 Mbit/s self-synchronizing **Directive conformity** Electromagnetic compatibility Directive 2014/30/EU EN 61326-1 Directive 2011/65/EU (RoHS) IEC/EN 63000 Standard conformity Degree of protection IEC 60529 **Ambient conditions** -25 ... 70 °C (-13 ... 158 °F) Ambient temperature Storage temperature -30 ... 80 °C (-22 ... 176 °F) air humidity max. 96 % Salt spray resistant to EN 60068-2-52 Climatic conditions Oscillation (Sine): 5 g, 10 - 1000 Hz to EN 60068-2-6 Shock and impact resistance Shock (Half-sine): 30 g, 11 ms in accordance with EN 60068-2-27 **Mechanical specifications** 148 mm Housing length Housing width 105 mm Housing height 73 mm Degree of protection IP67 Read/write heads: shielded, 4-pin, M12 connector Power supply: M12 connector Connection Protective earth: M6 earthing screw PROFIBUS: M12 connector, B-coded Material Housing powder coated aluminum Installation snap-on to 35 mm standard rail or screw fixing Mass approx. 1000 g

Connection



Assembly



Accessories

16	V1-G-2M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
66	V1-G-10M-PUR-ABG- V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
	V15B-G-5M-PUR-ABG- V15B-G	PROFIBUS bus cable M12 socket straight to M12 plug straight B-coded, 5-pin, PUR cable 2-core violet, shielded
6/	V1-G-5M-PUR	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey
66	V1-G-5M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
6/	V1-G-5M-PUR-ABG	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey, shielded
	ICZ-3T-0,3M-PUR ABG- V15B-G	Y connection cable for PROFIBUS

Accessories



ICZ-2T/TR-0,2M-PUR ABG-V15B-G Terminal cable for PROFIBUS with terminal resistor