




Inductive sensor NBN5-11K8-N-V8

- 5 mm non-flush



Dimensions



Technical Data

General specifications		
Switching function		Normally closed (NC)
Output type		NAMUR
Rated operating distance	s_n	5 mm
Installation		non-flush
Assured operating distance	s_a	0 ... 4.05 mm
Output type		2-wire
Nominal ratings		
Operating voltage	U_B	5 ... 15 V
Switching frequency	f	0 ... 2000 Hz
Hysteresis	H	0.05 ... 0.75
Current consumption		
Measuring plate not detected		min. 2.7 mA
Measuring plate detected		≤ 1.8 mA
Functional safety related parameters		
MTTF _d		8162 a
Mission Time (T _M)		20 a

Release date: 2023-09-13 Date of issue: 2023-09-13 Filename: 130051_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

pf PEPPERL+FUCHS

Technical Data

Diagnostic Coverage (DC)	0 %
Approvals and certificates	
UL approval	cULus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated ≤36 V
Ambient conditions	
Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Mechanical specifications	
Connection type	Solder connection
Housing material	PA
Degree of protection	IP67

Connection



Release date: 2023-09-13 Date of issue: 2023-09-13 Filename: 130051_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".