


Single head system



**Dimensions** 



**Technical Data** 

General specifications			
Sensing range	30 500 mm		
Adjustment range	50 500 mm		
Dead band	0 30 mm		
Standard target plate	100 mm x 100 mm		
Transducer frequency	approx. 380 kHz		
Response delay	approx. 50 ms		
Indicators/operating means			
LED yellow	indication of the switching state flashing: program function object detected		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



1

Technical Data		
LED red		"Error", object uncertain
		in program function: No object detected
Electrical specifications		
Operating voltage	UB	10 30 V DC , ripple 10 $\%_{\rm SS}$
No-load supply current	I <sub>0</sub>	≤ 50 mA
Input		
Input type		1 program input, operating range 1: $-U_B \dots +1 V$ , operating range 2: $+4 V \dots +U_B$ input impedance: $> 4.7 k\Omega$ ; program pulse: $\ge 1 s$
Output		
Output type		2 switch outputs PNP, NO/NC
Rated operating current	I <sub>e</sub>	2 x 100 mA , short-circuit/overload protected
Voltage drop	$U_d$	≤ 3 V
Repeat accuracy		≤1 %
Switching frequency	f	max. 8 Hz
Range hysteresis	Н	1 % of the set operating distance
Temperature influence		± 1.5 % of full-scale value
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated $\leq$ 36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 5-pin
Housing diameter		18 mm
Degree of protection		IP67
Material		
Housing		brass, nickel-plated
Transducer		epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT
Mass		60 g
Factory settings		
Output 1		Switching point: 50 mm output function: Switch point operation mode output behavior: NO contact
Output 2		Switching point: 500 mm output function: Switch point operation mode output behavior: NC contact
Beam width		wide

# Connection

Standard symbol/Connections:

(version E23, pnp)				
		1	(BN)	+ U <sub>R</sub>
		5	(GY)	<ul> <li>Teaching input</li> </ul>
U		4	(BK)	Switch output 1
	] [	2	(WH)	
ľ		3		Switch output 2
		_		U <sub>B</sub>

Core colours in accordance with EN 60947-5-2.

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

**F**PEPPERL+FUCHS

### **Connection Assignment**




Wire colors in accordance with EN 60947-5-2


1 2	BN WH	(brown) (white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

### **Characteristic Curve**

### Characteristic response curve



### Programmed switching output function



Accessories					
« (O)	UB-PROG3	Programming unit			
	ОМН-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm			

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



## UB500-18GM75-E23-V15

Acces	sories	
	BF 18	Mounting flange, 18 mm
	BF 18-F	Plastic mounting adapter, 18 mm
CO CO	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
C	UVW90-K18	Ultrasonic -deflector
000	M18K-VE	Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors
ø /	V15-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
<b>«</b> //	V15-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 5-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

4

### Programming procedure

The sensor features two switch outputs with one programmable switch point, each. Programming the switch points is done by applying the supply voltage -U<sub>B</sub> (switch output 1) or +U<sub>B</sub> (switch output 2) to the Teach-In input. The supply voltage must be applied to the Teach-In input for at least 1 s. LEDs indicate whether the sensor has recognized the target during the programming procedure.

#### Note:

Switching points may only be specified directly after Power on. A time lock secures the adjusted switching points against unintended modification 5 minutes after Power on. To modify the switching points later, the user may specify the desired values only after a new Power On.

#### Note:

If a programming adapter UB-PROG3 is used for the programming procedure, button A1 is assigned to -U<sub>B</sub> and button A2 is assigned to +U<sub>B</sub>.

#### Programming switch ouputs

#### Switch point for switch output 1

- 1. Place the target at the desired switch point position of switch output 1
- 2. Program the switch point by applying -U<sub>B</sub> to the Teach-In input (corresponding yellow LED flashes)
- 3. Disconnect the Teach-In input from -U<sub>B</sub> to save the switch point

#### Switch point for switch output 2

- 1. Place the target at the desired switch point position of switch output 2
- 2. Program the switch point by applying +UB to the Teach-In input (corresponding yellow LED flashes)
- 3. Disconnect the Teach-In input from +U<sub>B</sub> to save the switch point

#### Programming detection of object presence

- 1. Cover the sensor face with hand or remove all objects from sensing range
- 2. Apply -U<sub>B</sub> to the Teach-In input (red LED flashes)
- 3. Disconnect the Teach-In input from -U<sub>B</sub>
- 4. Apply +U<sub>B</sub> to the Teach-In input (red LED flashes)
- 5. Disconnect the Teach-In input from  $+U_B$

Note: Only one switch output can be configured for detection of presence of objects. If the sensor detects an object within the maximum detection range, the switch output switches.

#### Adjusting the sound cone characteristics:

The ultrasonic sensor enables two different shapes of the sound cone, a wide angle sound cone and a small angle sound cone.

#### 1. Small angle sound cone

- switch off the power supply
- connect the Teach-In input wire to -U<sub>B</sub>
- switch on the power supply
- the red LED flashes once with a pause before the next.
- yellow LED: permanently on: indicates the presence of an object or disturbing object within the sensing range
- disconnect the Teach-In input wire from -U<sub>B</sub> and the changing is saved

#### 2. Wide angle sound cone

- switch off the power supply
- connect the Teach-In input wire with +U<sub>B</sub>
- switch on the power supply
- the red LED double-flashes with a long pause before the next.
- yellow LED: permanently on: indicates an object or disturbing object within the sensing range
- disconnect the Teach-In input wire from +U<sub>B</sub> and the changing is saved

# **Factory Setting**

### Factory settings

See technical data.

## Indication

The sensor provides LEDs to indicate various conditions.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information



5

-Ò- pause -Ò-

ĿŎ: ÷Čpause

## Ultrasonic sensor

### UB500-18GM75-E23-V15

	Red LED	Yellow LED 1	Yellow LED 2
During Normal operation			
Proper operation	Off	Switching state output 1	Switching state output 2
Interference (e.g. compressed air)	On	remains in previous state	remains in previous state
Programming of output 1			
Object detected	Off	Flashes	Off
No object detected	Flashes	Off	Off
Object uncertain (programming invalid)	On	Off	Off
Programming of output 2			
Object detected	Off	Off	Flashes
No object detected	Flashes	Off	Off
Object uncertain (programming invalid)	On	Off	Off

# **Installation Conditions**

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF18, BF18-F or BF 5-30 must be used.

In case of direct mounting of the sensor in a through hole using the steel nuts, it has to be fixed at the middle of the housing thread. If a fixation at the front end of the threaded housing is required, plastic nuts with centering ring (accessories) must be used.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

