

Optical data coupler LS610-DA-IBS/F1






- No parameterization
- Usable up to detection range 0
- Line indicator for signal strength





Optical data coupler for INTERBUS, 120 m detection range, infrared light, M12 plug

Dimensions





Technical Data

General specifications 0 ... 120 m Effective detection range Threshold detection range 140 m modulated infrared light Light type Diameter of the light spot 2 m at a distance of 100 m 1.1 ° Angle of divergence Ambient light limit > 10000 Lux Functional safety related parameters 260 a MTTF_d Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Data flow indicator LED green: emitter LED yellow: receiver Function indicator alignment aid: flashing front red LED Signal strength (8 LED: Red, yellow, green) **Electrical specifications** Operating voltage U_B 18 ... 30 V DC No-load supply current 200 mA I_0 Data rate 0 ... 2 MBit/s F1 = 8.25 MHz Operation frequency Interface Interface type RS 422, galvanically isolated Output Pre-fault indication output 1 PNP (switches if there is sufficient stability control) short-circuit protected, max. 200 Conformity Product standard EN 60947-5-2 Approvals and certificates EAC conformity TR CU 020/2011 Approvals CE, cULus **Ambient conditions** -10 ... 50 °C (14 ... 122 °F) Ambient temperature -20 ... 70 °C (-4 ... 158 °F) Storage temperature



Mechanical specifications

Degree of protection

Connection

Material

Mass

Housing Optical face IP65


ABS / PC


plastic


700 g

4-pin, M12x1 connector, standard (supply) , 5-pin, M12x1 connector, B-coded (Remote Bus In) , 5-pin, M12x1 socket, B-coded (Remote Bus Out)

Connection Assignment








Plug M12 x 1, 4-pin A-coded

Characteristic Curve



Accessories

	V15-G-PG9	Female connector, M12, 5-pin, field attachable
00	Funktionserdung LS610/VDM100 Zubehoer	Function grounding for LS610 / LS611 / VDM100 series
	Schutzkappe LS610 Zubehoer	M12 protective cap set (connector + socket) for series LS610 / LS611
	OMH-LS610-01	Mounting bracket for optical data coupler

Accessories OMH-LS610-01 Mounting bracket for optical data coupler OMH-LS610-02 Direct mounting set consisting of 4 x M4 threaded inserts OMH-LS610-03 Mounting bracket with deviation mirror for optical data coupler OMH-LS610-32 Mounting bracket for optical data coupler and distance measurement devices


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Additional Information

Product description

The LS610-DA-IBS is a device for serial data transmission in INTERBUS systems with transmision rates of up to 2 MBit/sec and ranges up to 240 m. For data rates and operating ranges lower than these values, the device can also be used with no problems. For one data transmission connection, an LS 610-DA-IBS unit with a mean frequency of F1 **and** an LS 610-DA-IBS unit with mean frequency F2 are required.

The LS610-DA-IBS is intended for the direct connection of Interbus S units ("extension of bus cables"). It contains no bus connection logic, and is thus not suited for spur line installations. For this reason, only one of the M12 connectors should be used at a time




Data transmission

Data is transmitted in both directions using modulated infrared light. The information carried on the incoming bus is modulated on the carrier signal in real time using frequency shift keying (FSK). In the reciever, the corresponding demodulation is performed and the data is output on the outgoing bus. The complete transmission process is performed using no protocols.

The LS610 DA-IBS includes level-type regeneration as well as complete voltage isolation of the data transmission circuits from the power supply.

Function displays/function reserves

For alignment, there is an alignment LED on the unit's face which is visible from a distance. As soon as a receiver detects the transmission light of the opposite unit, the blink frequency of the alignment aid is lowered. When it is extinguished, this signals that the units are optimally aligned with one another, and enough functional reserve is available. For fine adjustment, the data system is equipped with a bar graph display (signal display) which enables optimal alignment.



Connection between display and operational status

If the bus is active, a yellow LED "RX" is lit for received data and a green LED "TX" for transmitted data.

Installation

Installation is done with the corresponding accessories, for instance, OMH-LS610-01 for wall mounting.

The x/y adjustment is premounted at the factory. It is fastened to the mounting bracket in the desired transmission direction ($\pm 90^{\circ}$ rotation possible) with the two M4 screws and a central M6 screw. The middle screw is for fastening after adjustment and should only be tightened afterwards.

The data photo sensor is inserted into the notches of the adjustment device while holding both of the front bolts together with holding tabs. After insertion, the bolts are released and hold the unit securely by springing back.

Using the two adjustment screws (Inbus 5 mm), the transmission axis can now be directed in the X and Y directions, and the adjustment fixed in place by tightening the middle screw.

LS610-DA-IBS/F1