

Place Holder Barrier KFD0-LGH-GN

- K-System place holder module
- Housing width 20 mm
- Marshalling for field and control side circuits
- Configurable via plug-in jumpers


Place holder barrier for KF modules



Function

The device is used in cable distribution cables. The device improves accessibility and compactness within a switch cabinet. Different configurations are possible by using wire jumpers. The wire jumpers are located in the device. To configure the device, you have to open the device.

Connection



Zone 2

Technical Data

Electrical specifications

Rated voltage	U_r	$\leq 50 \text{ V}$
Rated current	I_r	$\leq 2 \text{ A}$

Indicators/settings

Configuration	via internal wire jumpers
Labeling	space for labeling at the front

Conformity

Degree of protection	IEC 60529
----------------------	-----------

Ambient conditions

Ambient temperature	$-20 \dots 60 \text{ }^\circ\text{C}$ ($-4 \dots 140 \text{ }^\circ\text{F}$)
---------------------	---

Mechanical specifications

Degree of protection	IP20
----------------------	------

Technical Data

Connection	screw terminals
Mass	approx. 120 g
Dimensions	20 x 107 x 115 mm (0.8 x 4.2 x 4.5 inch) (W x H x D) , housing type B1
Mounting	on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with hazardous areas	
Certificate	PF 08 CERT 1214 X
Marking	Ⓜ II 3G Ex nA IIC T4 Gc
Directive conformity	
Directive 2014/34/EU	EN 60079-0:2012+A11:2013 , EN 60079-15:2010
General information	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com .

Assembly

Front view

