

Ultrasonic sensor


UC2000-30GM-IUR2-T-V15

- Parameterization interface for the application-specific adjustment of the sensor setting via the service program ULTRA 3000
- Analog current and voltage output
- Synchronization options
- Adjustable acoustic power and sensitivity
- Temperature compensation

Single head system



Dimensions



Technical Data

General specifications	
Sensing range	80 2000 mm
Adjustment range	120 2000 mm
Dead band	0 80 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 175 kHz
Response delay	65 ms minimum 195 ms factory setting
Indicators/operating means	
LED green	solid: Power-on flashing: Standby mode or program function object detected


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Technical Data					
LED yellow 1		solid: object in evaluation range			
		flashing: program function			
LED yellow 2		solid: object in detection range flashing: program function			
LED red		solid: temperature/program plug not connected flashing: fault or program function object not detected			
Temperature/TEACH-IN connector		Temperature compensation , Evaluation range programming , output function setting			
Electrical specifications					
Operating voltage	U _B	10 30 V DC , ripple 10 %ss			
Power consumption	P_0	≤ 900 mW			
Time delay before availability	t _v	≤ 500 ms			
Interface					
Interface type		RS 232, 9600 Bit/s , no parity, 8 data bits, 1 stop bit			
Input/Output					
Synchronization		bi-directional 0 level -U _B +1 V 1 level: +4 V+U _B input impedance: > 12 KOhm synchronization pulse: \geq 100 μ s, synchronization interpulse period: \geq 2 ms			
Synchronization frequency					
Common mode operation		max. 30 Hz			
Multiplex operation		\leq 30 Hz / n , n = number of sensors , n \leq 5			
Output					
Output type		1 current output 4 20 mA 1 voltage output 0 10 V			
Resolution		evaluation range [mm]/4000, but ≥ 0.35 mm			
Deviation of the characteristic curve		≤ 0.2 % of full-scale value			
Repeat accuracy		≤ 0.1 % of full-scale value			
Load impedance		current output: ≤ 500 Ohm voltage output: ≥ 1000 Ohm			
Temperature influence		≤ 2 % from full-scale value (with temperature compensation) ≤ 0.2 %/K (without temperature compensation)			
Compliance with standards and directives		_ 0.2 /a.r. (minor temperature 00.mpo.loano)			
Standard conformity					
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 EN 60947-5-7:2003 IEC 60947-5-7:2003			
Approvals and certificates					
UL approval		cULus Listed, General Purpose			
CCC approval		CCC approval / marking not required for products rated ≤36 V			
Ambient conditions					
Ambient temperature		-25 70 °C (-13 158 °F)			
Storage temperature		-40 85 °C (-40 185 °F)			
Mechanical specifications					
Connection type		Connector plug M12 x 1 , 5-pin			
Housing diameter		30 mm			
Degree of protection		IP65			
Material					
Housing		stainless steel (1.4305 / AISI 303) PBT plastic parts			
Transducer		epoxy resin/hollow glass sphere mixture; polyurethane foam			
Mass		210 g			
Factory settings					
Output		evaluation limit A1: 200 mm evaluation limit A2: 2000 mm rising ramp			

Connection

Standard symbol/Connection:

(version IU)



Core colors in accordance with EN 60947-5-2.


Connection Assignment

Connector V15




Characteristic Curve

Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

Analogue output function



Accessories



Release date: 2022-12-13 Date of issue: 2022-12-13 Filename: 129684_eng.pdf

BF 30

Mounting flange, 30 mm



BF 30-F

Plastic mounting adapter, 30 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

ULTRA3000 Software for ultrasonic sensors, comfort line UVW90-M30 Ultrasonic -deflector UVW90-K30 Ultrasonic -deflector M30K-VE Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors V15-G-2M-PVC Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey UC-30GM-R2 Interface cable V15-W-2M-PUR Female cordset single-ended M12 angled A-coded, 5-pin, PUR cable grey

Programming procedure

The sensor features 2 programmable analog outputs with programmable evaluation range. Programming the evaluation range and the operating mode is done either via the sensor's RS232 interface and ULTRA3000 software (see the ULTRA3000 software description) or by means of the programming plug at the sensor's back end which is described here.



Α2

Coded plug

E2/E3

Programming of Evaluation Range

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Place the target at the desired position for A1
- 5. Momentarily insert the programming plug in position A1 and then remove. This will program the position A1.
- 6. Place the target at the desired position for A2
- 7. Momentarily insert the programming plug in position A2 and then remove. This will program the position A2.

Notes:

- Removing the programming plug saves the new position into the device memory.
- The programming status is indicated by the LED. A flashing green LED indicates that the target is detected; a flashing red LED indicates that
 no target is detected.

Programming the Operation Mode

If the program mode is still activated, continue at number 4. If not, activate program mode by performing the sequence numbers 1 to 3.

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Insert the programming plug in position E2/E3. By removing and reinserting the plug, the user can toggle through the three different modes of operation. The selected mode is indicated by the LEDs as shown below:
 - Rising slope mode, LED A2 flashes
 - Falling slope mode, LED A1 flashes
 - · Zero line mode, LEDs A1 and A2 flash
- 5. Once the desired mode is selected, insert the programming plug in position T. This completes the programming procedure and saves the switch points and mode of operation.
- 6. The sensor now operates in normal mode.

Note

The programming plug also functions as the temperature compensation. If the programming plug has not been inserted in the T position within 5 minutes, the sensor will return to normal operating mode with the latest saved values, without temperature compensation.

Factory Setting

Factory settings


See technical data.

Indication

The sensor provides LEDs to indicate various conditions.

₹
2
2
Φ
*
38
8
Ξ
ഉ
a
ũ
≓
3
÷
5
ä
2022
ಜ
ē
S
. <u>∞</u>
₽
ŧ
å
8
Σ
57
ά
8
Ŋ
ē
g
ø
eas
흦
ď

	Green LED	Red LED	Yellow LED A1	Yellow LED A2
During Normal Operation - Temperature compensated - with removed programming	On Off	Off On	Object in evaluation range	Object in sensing range Object in sensing range
plug Interference (e.g. compressed air)	Off	Flashing	Object in evaluation range remains in previous state	remains in previous state
During Sensor Programming Evaluation limit A1:				
Object detected No object detected Evaluation limit A2:	Flashing Off	Off Flashing	Flashing Flashing	Off Off
Object detected No object detected Operation mode:	Flashing Off	Off Flashing	Off Off	Flashing Flashing
Rising slope mode Falling slope mode Zero line mode	On On On	Off Off Off	Off Flashing Flashing	Flashing Off Flashing
Standby	Flashing	Off	remains in previous state	remains in previous state



Commissioning

Synchronization

This sensor features a synchronization input for suppressing ultrasonic mutual interference ("cross talk"). If this input is not connected, the sensor will operate using internally generated clock pulses. It can be synchronized by applying an external square wave. The pulse duration must be \geq 100 μ s. Each falling edge of the synchronization pulse triggers transmission of a single ultrasonic pulse. If the synchronization signal remains low for \geq 1 second, the sensor will revert to normal operating mode. Normal operating mode can also be activated by opening the signal connection to the synchronization input (see note below).

If the synchronization input goes to a high level for > 1 second, the sensor will switch to standby mode, indicated by the green LED. In this mode, the outputs will remain in the last valid output state.

Note:

If the option for synchronization is not used, the synchronization input has to be connected to ground (0 V) or the sensor must be operated via a V1 cordset (4-pin).

The synchronization function cannot be activated during programming mode and vice versa.

The following synchronization modes are possible:

- 1. Several sensors (max. number see technical data) can be synchronized together by interconnecting their respective synchronization inputs. In this case, each sensor alternately transmits ultrasonic pulses in a self multiplexing mode. No two sensors will transmit pulses at the same time (see note below).
- 2. Multiple sensors can be controlled by the same external synchronization signal. In this mode the sensors are triggered in parallel and are synchronized by a common external synchronization pulse.
- 3. A separate synchronization pulse can be sent to each individual sensor. In this mode the sensors operate in external multiplex mode (see note below).
- 4. A high level (+U_B) on the synchronization input switches the sensor to standby mode.


Note:

Sensor response times will increase proportionally to the number of sensors that are in the synchronization string. This is a result of the multiplexing of the ultrasonic transmit and receive signal and the resulting increase in the measurement cycle time.

Additional Information

Note on communication with the UC-30GM-R2 interface cable

The UC-30GM-R2 interface cable allows for communication with the ultrasonic sensor using ULTRA3000 software. The cable creates a connection between a PC RS-232 interface and the programming plug socket on the sensor. When connecting to the sensor, make certain the plug is lined up correctly; otherwise no communication will be possible. The key of the cable's plug must be aligned to the groove of the socket on the sensor (not with the arrow symbol on the sensor).



Programmable parameters with the ULTRA3000 software

- Evaluation limits A1 and A2
- Operation mode
- Sonic speed
- Temperature offset (The inherent temperature-rise of the sensor can be considered in the temperature compensation)
- Expansion of the unusable area (for suppression of unusable area echoes)
- Reduction of the detection range (for suppression of remote range echoes)

Ultrasonic sensor

- · Time of measuring cycle
- Acoustic power (interference of the burst duration)
- Sensitivity
- · Behavior of the sensor in case of echo loss
- · Behavior of the sensor in case of a fault
- · Average formation via an allowed number of measuring cycles
- · Selection of the parameter set, RS 232 or manually

Note:

When connected to a PC and running the ULTRA3000 software, the sensor can act as a long term data logger as well.

Installation Conditions

If the sensor is installed in an environment where the temperature can fall below 0 °C, one of these mounting flanges must be used for mounting: BF30, BF30-F, or BF 5-30.

If it is intended to operate the sensor at - 25 °C, we recommend discussing the mounting situation with a Pepperl + Fuchs application specialist to ensure a trouble-free operation.

If the sensor is mounted in a through hole using the included steel nuts, it must be mounted at the middle of the threaded housing. If it must be mounted at the front end of the threaded housing, plastic nuts with centering ring (optional accessories) must be used.