


Ultrasonic sensor UB200-12GM-U-V1

- Analog output 0 ... 10 V
- Very small unusable area
- Measuring window adjustable
- Program input
- Temperature compensation

Single head system



Dimensions



Technical Data


General specifications	
Sensing range	15 200 mm
Adjustment range	20 200 mm
Dead band	0 15 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 400 kHz
Response delay	approx. 30 ms
Indicators/operating means	
LED yellow	solid yellow: object in the evaluation range yellow, flashing: program function, object detected

Technical Data		
LED red		solid red: Error red, flashing: program function, object not detected
Electrical specifications		
Operating voltage	U_B	15 30 V DC , ripple 10 %ss
No-load supply current	I ₀	≤ 30 mA
Input		
Input type		1 program input lower evaluation limit A1: -U _B +1 V, upper evaluation limit A2: +4 V +U _B input impedance: > 4.7 k Ω , pulse duration: \geq 1 s
Output		
Output type		1 analog output 0 10 V
Resolution		0.17 mm
Deviation of the characteristic curve		± 1 % of full-scale value
Repeat accuracy		\pm 0.5 % of full-scale value
Load impedance		> 2 kOhm
Temperature influence		± 1.5 % of full-scale value
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 EN 60947-5-7:2003 IEC 60947-5-7:2003
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing diameter		12 mm
Degree of protection		IP67
Material		
Housing		brass, nickel-plated
Transducer		epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT
Mass		25 g

Connection

Standard symbol/Connections:

(version U)



Core colours in accordance with EN 60947-5-2.

UB200-12GM-U-V1 Ultrasonic sensor

Connection Assignment




Wire colors in accordance with EN 60947-5-2

BN (brown) 2 WH (white) 3 BU (blue) BK (black)


Characteristic Curve

Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

Programming the analog output mode



Programming

Adjusting the evaluation limits

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage -UB or +UB to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with -UB, A2 with +UB. Five different output functions can be set:

1. Window mode, normally-open function

- 2. Window mode, normally-closed function
- 3. One switching point, normally-open function
- 4. One switching point, normally-closed function



Ultrasonic sensor UB200-12GM-U-V1

Programming

5. Detection of object presence

TEACH-IN window mode, normally-open function

- · Set target to near switching point
- TEACH-IN switching point A1 with -UB
- · Set target to far switching point
- · TEACH-IN switching point A2 with +UB

TEACH-IN window mode, normally-closed function

- · Set target to near switching point
- TEACH-IN switching point A2 with +UB
- · Set target to far switching point
- TEACH-IN switching point A1 with -UB

TEACH-IN switching point, normally-open function• Set target to near switching point

- TEACH-IN switching point A2 with +UB
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB

TEACH-IN switching point, normally-closed function

- · Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Cover sensor with hand or remove all objects from sensing range
- · TEACH-IN switching point A2 with +UB

TEACH-IN detection of objects presence

- · Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB
- · TEACH-IN switching point A2 with +UB

LED Displays

Displays in dependence on operating mode	Red LED	Yellow LED
TEACH-IN switching point: Object detected No object detected Object uncertain (TEACH-IN invalid)	flashes	flashes off off
Normal operation	off	Switching state
Fault	on	Previous state

Accessories

21	UB-PROG2	Programming unit
300	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
	BF 12	Mounting flange, 12 mm
	BF 12-F	Plastic mounting adapter, 12 mm
6/	V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey
61	V1-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey
an a	UVW90-M12	Ultrasonic -deflector
00	M12K-VE	Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors



Additional Information

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF 12, BF 12-F or BF 5-30 must be used. In case of direct mounting of the sensor in a through hole, it has to be fixed at the middle of the housing thread.

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Pepperl+Fuchs Group www.pepperl-fuchs.com

5