

# Inductive sensor NCB50-FP-E2-P4-V1

- Comfort series
- 50 mm flush
- 3-wire DC










#### **Dimensions**




## **Technical Data**

General specifications		
Switching function		Normally open (NO)
Output type		PNP
Rated operating distance	Sn	50 mm
Installation		flush
Output polarity		DC
Assured operating distance	Sa	0 40.5 mm
Reduction factor r <sub>Al</sub>		0.38
Reduction factor r <sub>Cu</sub>		0.35
Reduction factor r <sub>304</sub>		0.83

Technical Data		
Output type		3-wire
Nominal ratings		
Operating voltage	U <sub>B</sub>	10 60 V DC
Switching frequency	f	0 80 Hz
Hysteresis	Н	typ. 3 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	≤3 V
Operating current	IL	0 200 mA
Off-state current	l <sub>r</sub>	0 0.5 mA
No-load supply current	Io	≤ 20 mA
Time delay before availability	$t_{v}$	≤ 300 ms
Operating voltage indicator		LED, green
Switching state indicator		LED, yellow
Functional safety related parameters		
MTTF <sub>d</sub>		940 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
Compliance with standards and directives	s	
Standard conformity		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus Listed, General Purpose
CCC approval		Certified by China Compulsory Certification (CCC)
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing material		PBT
Sensing face		PBT
Housing base		metal
Degree of protection		IP68

#### Connection



## **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

### **Mounting**

These sensors are especially designed for embeddable mounting in conveyor floors. Due to its precise location in metal base plates the sensor is afforded a high degree of mechanical protection. No clearance is required between the sensor and the base plate, avoiding the need for protective guarding to prevent possible foot injury.

The large sensing range ensures positive detection, and thus provides consistent control and monitoring of the conveyor.



Warning!

Once the metal screening has been removed, the sensor can no longer be embeddable mounted.