




Barcode scanner VB34-2500-OM-P

- Version with integrated oscillating mirror
- Optimized for the requirements of the automobile industry
- Dynamic focusing system
- Fast Lonworks interface for master/slave configurations
- Display and keypad for parameter settings

Barcode scanner with PROFIBUS interface



Dimensions



Technical Data

General specifications

Light source	laser diode
Light type	modulated visible red light

Release date: 2023-09-05 Date of issue: 2023-09-05 Filename: 180334_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Laser nominal ratings		
Note		LASER LIGHT , DO NOT STARE INTO BEAM
Laser class		2
Wave length		650 nm
Beam divergence		< 1.5 mrad
Pulse length		0.097 ms
Repetition rate		500 Hz
max. pulse energy		0.39 μ J
Scan rate		600 ... 1200 s ⁻¹ , programmable
Read distance		450 ... 2000 mm
Oscillating mirror		Deflection: -2.5° ... 37.5° , parameterizable Oscillation frequency: 0 ... 19 Hz, programmable
Resolution		max: 0.2 mm (8 mils)
Indicators/operating means		
Operation indicator		LED green: Power on , LED yellow: Trigger phase active (PHASE ON)
Data flow indicator		LED green flashing: Data transfer carried out (TX-DATA)
Control elements		Keypad (3 membrane keys) for parameter settings on the LCD display
Parameterization indicator		LC display
Electrical specifications		
Operating voltage	U _B	15 ... 30 V DC
Power consumption	P ₀	max. 20 W
Interface		
Interface type		serial RS-232 and RS-485 up to 115.2 kbit/s , PROFIBUS
Input 1		
Input type		3 digital inputs and external trigger
Output		
Switching voltage		max. 30 V DC
Switching current		max. 50 mA
Voltage drop	U _d	0.3 V at load current \leq 10 mA
Compliance with standards and directives		
Directive conformity		EMC Directive 2004/108/EC
Standard conformity		
Noise immunity		EN 61000-6-2:2005
Emitted interference		EN 55022
Electrical safety		EN 60950-1:2006
Laser class		IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007
Ambient conditions		
Ambient temperature		0 ... 40 °C (32 ... 104 °F)
Storage temperature		-20 ... 70 °C (-4 ... 158 °F)
Relative humidity		90 % , noncondensing
Shock resistance		IEC 68-2-27 Test EA 30G; 11 ms; 3 impacts on each axis
Vibration resistance		IEC 68-2-6 Test FC 1.5 mm ; 10 ... 55 Hz ; 2 hours on each axis
Mechanical specifications		
Degree of protection		IP64
Connection		Interface (primary, secondary) : 26-pin Sub-D connector , Lonworks: 9-pin Sub-D socket , PROFIBUS: 9-pin Sub-D socket
Material		
Housing		Aluminum
Mass		2000 g

Connection



Pin	Name	Function
1	Schirm	The shield is interfaced with chassis ground via a capacitor internally.
20	RXAUX	Receive data of RS232 interface (earth-related)
21	TXAUX	Transmission data of RS232 interface (earth-related)
8	Out1+	Plus lead of digital output 1
22	Out1-	Minus lead of digital output 1
11	Out2+	Plus lead of digital output 2
12	Out2-	Minus lead of digital output 2
16	Out3A	Digital output 3 - polarity commutable
17	Out3B	Digital output 3 - polarity commutable
18	Ext_TRIG. A	External trigger (polarity commutable)
19	Ext_TRIG. B	External trigger (polarity commutable)
6	IN 2A	Input signal 2 (polarity commutable)
10	IN 2B	Input signal 2 (polarity commutable)
14	IN 3A	Input signal 3 (polarity commutable)
15	IN 4A	Input signal 4 (polarity commutable)
24	IN_REF	Common earth reference for IN3 and IN4 (polarity commutable)
9, 13	VS	Supply voltage - plus
23, 25, 26	GND	Supply voltage - minus (earth)


Electrical connections of the connector for primary interface

Pin	RS232	RS485 full-duplex	RS485 half-duplex
2	TX	TX485 +	RTX485 +
3	RX	RX485 +	
4	RTS	TX485 -	RTX485 -
5	CTS	RX485 -	
7	GND_ISO	GND_ISO	GND_ISO

Characteristic Curve

Reading characteristics VB34*OM*

read characteristics at resolution: 0.20 mm (8 mils)
in mm




NOTE
(0.0) is the center of the laser beam output window.

Release date: 2023-09-05 Date of issue: 2023-09-05 Filename: 180334_eng.pdf

Characteristic Curve

Reading characteristics VB34*OM*


read characteristics at resolution: 0.375 mm (15 mils)
in mm



NOTE
(0.0) is the center of the laser beam output window.

Reading characteristics VB34*OM*

read characteristics at resolution: 0.5 mm (20 mils)
in mm



NOTE
(0.0) is the center of the laser beam output window.

Safety Information



**LASERLICHT
LASER LIGHT
LUMIÈRE LASER**

**NICHT IN DEN STRAHL BLICKEN
DO NOT STARE INTO BEAM
NE PAS REGARDER LE FAISCEAU**

**LASER KLASSE 2
CLASS 2 LASER PRODUCT
PRODUIT LASER CLASSE 2**

Safety Information

Laser Class 2 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people!
 Caution: Do not look into the beam!
 Maintenance and repairs should only be carried out by authorized service personnel!
 Attach the device so that the warning is clearly visible and readable.
 Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Release date: 2023-09-05 Date of issue: 2023-09-05 Filename: 180334_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".