



## Inductive sensor

### NBB4-F1-E3

- 4 mm flush
- 3-wire DC



## Dimensions



## Technical Data

| General specifications       |       |                            |
|------------------------------|-------|----------------------------|
| Switching function           |       | Normally closed (NC)       |
| Output type                  |       | PNP                        |
| Rated operating distance     | $s_n$ | 4 mm                       |
| Installation                 |       | flush                      |
| Output polarity              |       | DC                         |
| Assured operating distance   | $s_a$ | 0 ... 3.24 mm              |
| Reduction factor $r_{Al}$    |       | 0.4                        |
| Reduction factor $r_{Cu}$    |       | 0.45                       |
| Reduction factor $r_{304}$   |       | 0.8                        |
| Reduction factor $r_{Brass}$ |       | 0.55                       |
| Output type                  |       | 3-wire                     |
| Nominal ratings              |       |                            |
| Operating voltage            | $U_B$ | 10 ... 30 V DC             |
| Switching frequency          | $f$   | 0 ... 1400 Hz              |
| Hysteresis                   | $H$   | typ. 5%                    |
| Reverse polarity protection  |       | reverse polarity protected |

Release date: 2023-12-08 Date of issue: 2023-12-08 Filename: 184368\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

## Technical Data

|   |           |  |
|---|-----------|--|
| Short-circuit protection                        |           | pulsing  |
| Voltage drop                                    | $U_d$     | $\leq 2.5$ V   |
| Rated insulation voltage                        | $U_{BIS}$ | 60 V   |
| Operating current                               | $I_L$     | 0 ... 250 mA   |
| Off-state current                               | $I_r$     | 0 ... 0.01 mA typ. 0.1 $\mu$ A at 25 °C                            |
| No-load supply current                          | $I_0$     | $\leq 15$ mA   |
| Switching state indicator                       |           | LED, yellow  |
| <b>Functional safety related parameters</b>     |           |  |
| MTTF <sub>d</sub>                               |           | 1640 a   |
| Mission Time (T <sub>M</sub> )                  |           | 20 a   |
| Diagnostic Coverage (DC)                        |           | 0 %  |
| <b>Compliance with standards and directives</b> |           |  |
| Standard conformity                             |           |  |
| Standards                                       |           | EN 60947-5-2:2007<br>IEC 60947-5-2:2007                            |
| <b>Approvals and certificates</b>               |           |  |
| Protection class                                |           | II   |
| Rated insulation voltage                        | $U_i$     | 60 V   |
| Rated impulse withstand voltage                 | $U_{imp}$ | 800 V  |
| UL approval                                     |           | cULus Listed, General Purpose                                      |
| CCC approval                                    |           | CCC approval / marking not required for products rated $\leq 36$ V |
| <b>Ambient conditions</b>                       |           |  |
| Ambient temperature                             |           | -25 ... 70 °C (-13 ... 158 °F)                                     |
| <b>Mechanical specifications</b>                |           |  |
| Connection type                                 |           | cable PVC , 2 m  |
| Core cross section                              |           | 0.5 mm <sup>2</sup>  |
| Housing material                                |           | PA   |
| Sensing face                                    |           | PA   |
| Degree of protection                            |           | IP67   |
| Tightening torque, fastening screws             |           | Threading M3 max: 1.1 Nm   |

## Connection Assignment

