

Retroreflective sensor

RL28-55-LAS-2840/47/115b



- Visible red light, pulsed LASER light
- High operating range
- Ultra bright LEDs for power on, weak signal indication and switching state
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II

Retroreflective sensor with polarization filter












Dimensions



Technical Data


General specifications		
Effective detection range	0 30 m	
Reflector distance	0.3 30 m	

Technical Data

Threshold detection range 42 m MH82 reflector Reference target Light source laser diode Light type modulated visible red light Polarization filter Laser nominal ratings LASER LIGHT. DO NOT STARE INTO BEAM Note Laser class Wave length 650 nm Beam divergence < 1.5 mrad Pulse length approx. 4.5 µs Repetition rate approx. 6 kHz ... 20 kHz max. pulse energy 4 n.J Diameter of the light spot approx. 45 mm at 30 m Opening angle Emitter: < 0.1 ° Receiver: < 2 ° 50000 Lux Ambient light limit Functional safety related parameters MTTF_d 560 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green 2 LEDs yellow, light up when light beam is free, flash when falling short of the stability control, off when light beam is interrupted Function indicator Control elements sensitivity adjustment (Adjustment to < 25% of the effective operating range) **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC Ripple max. 10 % No-load supply current ≤ 35 mA I_0 Protection class II, rated insulation voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output light-on Switching type 2 PNP, complementary, short-circuit protected, reverse polarity protected , open Signal output collectors Switching voltage max. 30 V DC max. 200 mA Switching current ≤ 2.5 V DC Voltage drop U_d Switching frequency f 1000 Hz Response time 0.5 ms Conformity Product standard EN 60947-5-2 EN 60825-1 Laser safety Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1 IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations FDA approval pursuant to Laser Notice No. 50, dated June 24, 2007 **Ambient conditions** -10 ... 50 °C (14 ... 122 °F) Ambient temperature Storage temperature -40 ... 60 °C (-40 ... 140 °F) **Mechanical specifications** Housing width 25.8 mm 88 mm Housing height

Housing depth 54.3 mm Degree of protection IP67 Connection fixed cable 230 mm with M12 x 1 male connector, 4-pin		
	Housing depth	54.3 mm
Connection fixed cable 230 mm with M12 x 1 male connector, 4-pin	Degree of protection	IP67
	Connection	fixed cable 230 mm with M12 x 1 male connector, 4-pin
Material	Material	
Housing Plastic ABS	Housing	Plastic ABS
Optical face Plastic pane	Optical face	Plastic pane
Mass 80 g	Mass	80 g

Connection



O = Light on


= Dark on

Connection Assignment



Wire colors in accordance with EN 60947-5-2

1 | BN (brown) 2 | WH (white) 3 | BU (blue) 4 | BK (black)



Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people!

Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories

6.	OMH-05	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-21	Mounting bracket: mounting aid for sensors in the RL* series
	OMH-22	Mounting aid for RL* series
	OMH-RLK29-HW	Mounting bracket for rear wall mounting

Accessories OMH-RL28-C Weld slag cover model REF-MH82 Reflector with Micro-structure, rectangular 82 mm x 60 mm, mounting holes