



## AS-Interface gateway

### VBG-PB-K25

- Gateway compliant with AS-Interface specification 3.0
- Compact stainless steel housing
- 7-segment display of addresses and error messages
- Connection to PROFIBUS DP
- Commissioning, without PROFIBUS communication
- All AS-Interface functions possible via PROFIBUS

## PROFIBUS gateway



## Function

The VBG-PB-K25 is a PROFIBUS Gateway in accordance with AS-Interface Specification 3.0 and to IP20. The compact construction makes it particularly suitable for use in the control cabinet.

The VBG-PB-K25 is a modular PROFIBUS Slave. This means, that the PROFIBUS configuration tool can be used to determine which data are to be transferred via PROFIBUS. The quantity of data to be transferred via PROFIBUS can be adapted by this means.


This gateway supports the acyclic communication of the PROFIBUS DP V1. With the help of this acyclic service a mail box in the gateway for both AS-Interface masters can be addressed, via which all data made available by the AS-Interface/PROFIBUS gateway can be accessed. Address assignment, acceptance of the set configuration, the setting of the PROFIBUS and baud rate are possible via push button. 7 LEDs, mounted on the front, indicate the current status of the AS-Interface network.

This gateway can be used to keep the commissioning of the AS-Interface circuit, as well as the test of the connected peripherals, completely separate from the commissioning of the PROFIBUS and the programming. Local operation using the LED display and the 2 buttons enables all the functions to be represented, which are covered by the other gateways via the AS-i Control Tools software.

### PLC functionality

Optionally the gateway is also available with PLC-functionality. Therefore you can order a code key VAZ-CTR additionally.

## Dimensions



## Technical Data

### General specifications

AS-Interface specification	V3.0
PLC-Functionality	activateable
Earth fault detection	EFD integrated
EMC monitoring	integrated
Diagnostics function	integrated
UL File Number	E223772

Release date: 2021-09-27 Date of issue: 2021-09-27 Filename: 187124\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com


**PF** PEPPERL+FUCHS

## Technical Data

Functional safety related parameters		
MTTF <sub>d</sub>		105 a at 30 °C
Indicators/operating means		
Display		address display, error message LED display, 3 digits, for addressing and error messages
LED PROFIBUS		PROFIBUS master detected; LED green
LED AS-i ACTIVE		AS-Interface operation normal; LED green
LED CONFIG ERR		configuration error; LED red
LED PRG ENABLE		autom. programming; LED green
LED POWER		voltage ON; LED green
LED PRJ MODE		projecting mode active; LED yellow
LED U AS-i		AS-Interface voltage; LED green
Switch SET		Selection and setting of a slave address
Button MODE		Mode selection PRJ-operation/save configuration/cursor
Electrical specifications		
Insulation voltage	U <sub>i</sub>	≥ 500 V
Rated operating voltage	U <sub>e</sub>	from AS-Interface
Rated operating current	I <sub>e</sub>	≤ 200 mA from AS-Interface
Interface		
Interface type		RS-485
Protocol		PROFIBUS DP V0 and V1
Transfer rate		9.6 kBit/s ... 12 MBit/s , Automatic baud rate detection
Connection		
PROFIBUS		Sub-D interface
AS-Interface		spring terminals, removable
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 62026-2:2013
Standard conformity		
Electromagnetic compatibility		EN 61000-6-2, EN 61000-6-4
Degree of protection		EN 60529:2000
AS-Interface		EN 62026-2:2013
Shock resistance		EN 61131-2
Ambient conditions		
Ambient temperature		0 ... 55 °C (32 ... 131 °F)
Storage temperature		-25 ... 85 °C (-13 ... 185 °F)
Mechanical specifications		
Housing length		120 mm
Housing width		45 mm
Housing depth		40 mm
Degree of protection		IP20
Mass		approx. 460 g
Construction type		Low profile housing , Stainless steel


Release date: 2021-09-27 Date of issue: 2021-09-27 Filename: 187124\_eng.pdf

Connection



At the cable for power supply no slaves or repeaters may be attached.  
 At the cable for AS-Interface circuit no power supplies or further masters may be attached.

Assembly



Accessories

	<b>VAZ-SW-ACT32</b>	Full version of the AS-I Control Tools including connection cable
	<b>VAZ-PB-SIM</b>	PROFIBUS master simulator
	<b>VAZ-PB-DB9-W</b>	PROFIBUS Sub-D Connector with switchable terminal resistance

Release date: 2021-09-27 Date of issue: 2021-09-27 Filename: 187124\_eng.pdf