



Retroreflective sensor MLV41-54-G/25/115/123/136



- Rugged series in corrosion-resistant metal housing
- Reliable recognition of reflective objects and clear glass
- Two machines in one: clear object detection or reflection operating mode with long range
- TEACH-IN switch for setting the contrast detection levels
- Automatic adjustment in case of soiling in contrast detection mode
- Resistant against noise: reliable operation under all conditions

Robust retroreflective sensor for glass detection, compact housing design, 5.2 m detection range, red light, light on, 2 push-pull outputs, fixed cable










Function

The unique and extremely popular design of the MLV41 series enables it be mounted correctly in confined areas and offers all the functions that are normally only found on larger phototelectric sensors. The MLV41 series comes with a range of functions. For example, highly visible status LEDs on the front and back, resistance to ambient light, crosstalk protection and universally applicable output stages that permit every possible switching logic and polarity to be realized. The enhanced resistance to ambient light ensures reliable operation even where modern energy-saving lamps with electronic ballasts are in use. The same applies where multiple devices are present, i.e. the use of a number of sensors in the same vicinity causes no problems.

Dimensions




	'	1		
-	nn			ta
ᆫ		ıcal		

General specifications	
Effective detection range	0 4 m in TEACH mode 0 5.2 m at switch position "N"
Reflector distance	0 4 m in TEACH mode 0 5.2 m at switch position "N"
Threshold detection range	6.5 m
Reference target	H85-2 reflector
Light source	LED
Light type	modulated visible red light, 660 nm
Polarization filter	yes
Angle deviation	max. ± 1°
Diameter of the light spot	approx. 100 mm at detection range 4 m
Opening angle	1.5 °
Ambient light limit	40000 Lux
Functional safety related parameters	
MTTF _d	900 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)
Function indicator	2 LEDs yellow for switching state, stability control, TEACH-IN and contrast detection mode

Technical Data Control elements 5-step switch for setting the contrast detection levels. 10 % - clean, water filled PET bottles 18 % - clear glass bottles 40 % - colored glass or opaque materials adjustable due to Teach-In switch Contrast detection levels **Electrical specifications** 10 ... 30 V DC Operating voltage U_B Ripple max. 10 % No-load supply current I_0 max. 35 mA Input Function input Ext. Teach-In input (ET) Output Signal output 2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected Switching voltage max. 30 V DC Switching current max. 100 mA Voltage drop U_{d} ≤ 2.5 V DC 1000 Hz Switching frequency f Response time 0.5 ms Conformity EN 60947-5-2 Product standard Approvals and certificates II, rated voltage \leq 50 V AC with pollution degree 1-2 according to IEC 60664-1 , functional insulation acc. to DIN EN 50178 Protection class **UL** approval cULus Listed 57M3 (Only in association with UL Class 2 power supply; Type 1 enclosure) CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -40 ... 60 °C (-40 ... 140 °F) Ambient temperature Storage temperature -40 ... 75 °C (-40 ... 167 °F) **Mechanical specifications** Housing width 31 mm Housing height 56.5 mm 13.6 mm Housing depth Degree of protection IP67 Connection 2 m fixed cable Material Housing Aluminum, Delta-Seal coated Optical face glass pane Mass 100 g




Connection Assignment




- O = Light on
- = Dark on

Assembly



- Operating display green
- 2 Functional display yellow
- 3 Teach-In switch
- Optical center emitter and receiver 4

Characteristic Curve



Accessories

E I	ОМН-09	Mounting bracket for Sensors series MLV41 for M12 rod mounting
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap
9	REF-VR10	Reflector, rectangular 60 mm x 19 mm, mounting holes
	ORR50G	Reflector, rectangular 50.9 mm x 60.9 mm, mounting holes, fixing strap and polarization filter
	OFR-100/100	Reflective tape 100 mm x 100 mm

Teach-In

Instructions for the Teach-In mode:

Step	Switch position	LED green	LED yellow	Time/ Frequen cy	Explanations/ Remarks
1	N	on	flashes	4/s	In switch position "N" aligned with reflector.
					Reflector detected without functional reserve.
	N	on	on	-	In switch position "N" aligned with reflector.
					Reflector detected with functional reserve (recommended).
2	Т	off/on	on	200 ms	A new switch position is indicated by the green LED going out briefly.
					This applies also for the selection of the other switch positions.
	Т	flashes	flashes	2.5/s	Slow alternating flashing: Teach-In process correctly executed.
					Max. duration of the Teach-In process: 2 s
	Т	flashes	flashes	8/s	Rapid alternating flashing: Teach-In process not correctly executed. (e.g. receiver signal not sufficient, sensor not correctly aligned with reflector).
					Status is terminated by turning switch to position N.
3/1	I	on	on	-	Contrast detection 10 % is activated. (e.g. clean PET bottles filled with water)
3/2	II	on	on	-	Contrast detection 18 % is activated. (e.g. bottles made of clear glass)
3/3	III	on	on	-	Contrast detection 40 % is activated. (e.g. tinted glass or intransparent materials)

Ext. TEACH input:

In switch position "T" it is possible to trigger a Teach-In process and to select the corresponding contrast detection level by the external application of a High pulse of a certain width:

l: 50 ms	(30 80 ms)
II: 150 ms	(120 180 ms)
III:250 ms	(220 280 ms)
N:350 ms	(320 380 ms)