

# 

# Retroreflective sensor





- Efficient Line in a short M18 plastic housing for standard applications
- Very high detection range
- 4 LEDs indicator for 360° visibility
- Optimized potentiometer design for a clear control button layout in the application
- Version with front optical face
- DC voltage version

Retroreflective sensor, M18 threaded housing design, plastic housing, front optical face, 6.5 m detection range, red light, dark on, DC version, NPN output, fixed cable









#### **Function**

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

# **Application**

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control


Material handling:

· Presence checks, target sensor, profile checks, trigger sensor

Automatic doors, gates and access systems, elevator:

- Secure detection for automatic door and gate systems
- · Monitoring function in turnstiles
- · Closing edge monitoring in elevators

# **Dimensions**



		1	1	-
IAC	nn	ıca	<b>L</b> -1	
		IUGI	 ( • I	


**General specifications** 

Gonoral opcomoditions	
Effective detection range	0 6.5 m
Reflector distance	0.05 6.5 m
Threshold detection range	8 m
Reference target	reflector C110-2
Light source	LED
Light type	modulated visible red light, 640 nm
Polarization filter	no
Diameter of the light spot	approx. 300 mm at 8 m
Opening angle	approx. 2 °
Optical face	frontal
Ambient light limit	30000 Lux
Functional safety related parameters	
MTTF <sub>d</sub>	920 a
Mission Time (T <sub>M</sub> )	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green, statically lit Power on
Function indicator	LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted
Electrical specifications	
Operating voltage	U <sub>B</sub> 10 30 V DC

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 188554\_eng.pdf


Technical Data		
No-load supply current	I <sub>0</sub>	< 20 mA
Output	10	~ LO 110 (
Switching type		dark-on
Signal output		1 NPN, short-circuit protected open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	Ud	≤ 1.5 V DC
Switching frequency	f	500 Hz
Response time	'	≤1 ms
Conformity		2 1 1116
Product standard		EN 60947-5-2
Approvals and certificates		EN 00947-3-2
Protection class		II, Rated insulation voltage ≤ 50 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		cULus Listed, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 60 °C (-13 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		PC
Optical face		PMMA
Cable		PVC
Mass		approx. 75 g

# **Connection Assignment**




- O = Light on
- = Dark on


# **Assembly**



1	Operating display green			
2	Signal display yellow			
4	Emitter			
5	Receiver			

# **Characteristic Curve**





#### **Accessories**

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 188554\_eng.pdf

0	CPZ18B03	Mounting Bracket with swivel nut
	BF 18	Mounting flange, 18 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

# **Accessories** BF 18-F Plastic mounting adapter, 18 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 $\dots$ 30 mm