

Thru-beam sensor



- Photoelectric sensor for detecting people, objects and vehicles
- Large construction with small housing
- Not sensitive to ambient light
- Version for universal voltages
- Relay output
- Version with accessories in scope of delivery

LA31/LK31/25/31/115 SET

Mid-range photoelectric sensors for detecting people, objects, and vehicles



Function

Series 31 is a range of cost-effective and, most importantly, reliable photoelectric sensors for standard applications in the fields of material handling and logistics, and for monitoring industrial doors, elevators, and automatic gates. The ultrasonic-welded plastic housing provides a high degree of protection, making these sensors ideal for tasks in harsh outdoor conditions. These sensors are currently the most compact "wide range power supply sensors" that can work with any DC and AC voltage between 24 V and 240 V. In addition to the robust technology, the sensors offer numerous product details that help the user with assembly, connection and operation.


Application

- · Monitoring closing edges of automatic industrial doors and elevators
- · Monitoring the swing range of automatic gates
- · Detecting and tracking objects in material handling

Release date: 2023-10-31 Date of issue: 2023-10-31 Filename: 189746_eng.pdf



Dimensions



Operating principle	color		-
Retroreflective sensor with polarisation filter	green	1	
Retroreflective sensor	blue		-
Diffusive mode sensor	white		
Thru-beam sensor	grey		
Diffusive mode sensor with background suppression	red	J	 J

Technical Data

System components	
Emitter	LA31/115
Receiver	LK31/25/31/115
General specifications	
Effective detection range	0 30 m
Threshold detection range	43 m
Light source	LED
Light type	modulated visible red light , 630 nm
Alignment aid	LED yellow: 1. LED illuminates: Sufficient light signal received, emitter and receiver alignment is correct 2. LED flashes: Reaching switching point 3. LED off: Light beam is interrupted or the alignment is out
Diameter of the light spot	approx. 800 mm at a distance of 30 m
Opening angle	Emitter: 0.5 ° , Receiver: 1.5 °
Ambient light limit	50000 Lux
Accessories provided	2 x Mounting bracket OMH-RL31-01 and mounting materials
Functional safety related parameters	
MTTF _d	790 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green: power on
Function indicator	LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Release date: 2023-10-31 Date of issue: 2023-10-31 Filename: 189746_eng.pdf

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

2


Technical Data		
Electrical specifications		
Operating voltage	U_B	24 240 V AC 12 240 V DC
No-load supply current	lo	Emitter: ≤ 40 mA Receiver: ≤ 3 mA
Power consumption	P ₀	Emitter: ≤ 1 VA Receiver: ≤ 1 VA
Output		
Switching type		light-on
Signal output		Relay, 1 alternator
Switching voltage		max. 250 V AC/DC
Switching current		max. 3 A
Switching power		DC: max. 150 W AC: max. 750 VA
Switching frequency	f	≤ 20 Hz
Response time		≤ 25 ms
Conformity		
Product standard		EN 60947-5-2
Compliance with standards and directives		
Standard conformity		
Standards		EN 62103
Approvals and certificates		
Protection class		II , rated voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN 50178, rated insulation voltage 240 V AC
CCC approval		Certified by China Compulsory Certification (CCC)
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		Emitter: 2 m fixed cable ,2-wire Receiver: 2 m fixed cable ,5-wire
Material		
Housing		Polycarbonate
Optical face		PMMA
Mass		Emitter: 116 g Receiver: 131 g

Connection Assignment




Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Assembly



1	Operating display	green		
2	Signal display yello			
3	B Emitter or receiver			

Characteristic Curve



Release date: 2023-10-31 Date of issue: 2023-10-31 Filename: 189746_eng.pdf

4

Thru-beam sensor

Application



Kit component						
	OMH-RL31-01	Mounting bracket				

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group www.pepperl-fuchs.com

