Thru-beam sensor

GD18-S/GV18-S/59/102/159





- Efficient Line in a short M18 plastic housing for standard applications
- Very high detection range
- 4 LEDs indicator for 360° visibility
- Sidelookerversion
- DC voltage version

Thru-beam sensor, M18 threaded housing design, plastic housing, side optical face, 12 m detection range, red light, dark on, DC version, NPN output, M12 plug









Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control


Material handling:

· Presence checks, target sensor, profile checks, trigger sensor

Automatic doors, gates and access systems, elevator:

- Secure detection for automatic door and gate systems
- · Monitoring function in turnstiles
- · Closing edge monitoring in elevators

Dimensions




_			_		
	chn	00	-		
				-	


System components		
Emitter		GD18-S/159
Receiver		GV18-S/59/102/159
General specifications		
Effective detection range		0 12 m
Threshold detection range		17.5 m
Light source		LED
Light type		modulated visible red light , 640 nm
Diameter of the light spot		approx. 650 mm at 17.5 m
Opening angle		approx. 2 °
Optical face		lateral
Ambient light limit		30000 Lux
Functional safety related parameters		
MTTF _d		630 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green, statically lit Power on
Function indicator		Receiver: LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve; OFF when light beam is interrupted
Electrical specifications		
Operating voltage	U _B	10 30 V DC
No-load supply current	I_0	< 20 mA
Output		

Technical Data Switching type dark-on Signal output 1 NPN, short-circuit protected open collector Switching voltage max. 30 V DC Switching current max. 100 mA U_{d} Voltage drop ≤ 1.5 V DC f 500 Hz Switching frequency Response time ≤1 ms Conformity Product standard EN 60947-5-2 Approvals and certificates Protection class II, Rated insulation voltage ≤ 50 V AC with pollution degree 1-2 according to IEC **UL** approval cULus Listed, Class 2 Power Source, Type 1 enclosure CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -25 ... 60 °C (-13 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Degree of protection Connection 3-pin, M12 x 1 connector Material Housing PC Optical face **PMMA** Connector plastic Mass approx. 10 g per device

Connection Assignment












Thru-beam sensor


Wire colors in accordance with EN 60947-5-2


1 | BN (brown) 3 | BU (blue) 4 | BK (black)

Assembly



Characteristic Curve





Accessories CPZ18B03 Mounting Bracket with swivel nut **BF 18** Mounting flange, 18 mm BF 18-F Plastic mounting adapter, 18 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm V11-G-2M-PUR Female cordset single-ended M12 straight A-coded, 3-pin, PUR cable grey