

Retroreflective sensor

GLV18-55-S/115/120



- Efficient Line in a short M18 plastic housing for standard applications
- Very high detection range
- 4 LEDs indicator for 360° visibility
- Sidelookerversion
- DC voltage version

Retroreflective sensor with polarization filter, M18 threaded housing design, plastic housing, side optical face, 3.5 m detection range, red light, light/dark on, DC version, 2 PNP outputs, fixed cable









Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control


Material handling:

· Presence checks, target sensor, profile checks, trigger sensor

Automatic doors, gates and access systems, elevator:

- Secure detection for automatic door and gate systems
- · Monitoring function in turnstiles
- · Closing edge monitoring in elevators

Dimensions



nnıcal	

General specifications		
Effective detection range		0 3.5 m
Reflector distance		0.05 3.5 m
Threshold detection range		4.5 m
Reference target		reflector C110-2
Light source		LED
Light type		modulated visible red light , 640 nm
Polarization filter		yes
Diameter of the light spot		approx. 160 mm at 4.5 m
Opening angle		approx. 2 °
Optical face		lateral
Ambient light limit		30000 Lux
Functional safety related parameters		
MTTF _d		920 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green, statically lit Power on
Function indicator		LED yellow: lights up when receiving the light beam ; flashes when falling short of the operating reserve; OFF when light beam is interrupted $\frac{1}{2} \int_{-\infty}^{\infty} \frac{1}{2} \left(\frac{1}{2} \int_{-$
Electrical specifications		
Operating voltage	U_B	10 30 V DC
No-load supply current	I_0	< 20 mA
Output		

Technical Data

Switching voltage max. 30 V DC
Switching current max. 100 mA

Voltage drop $U_d \leq 1.5 \text{ V DC}$

Switching frequency f 500 Hz
Response time ≤ 1 ms

Conformity

Product standard EN 60947-5-2

Approvals and certificates

Protection class II, Rated insulation voltage ≤ 50 V AC with pollution degree 1-2 according to IEC

60664-

UL approval cULus Listed, Class 2 Power Source
CCC approval CCC approval / marking not required for products rated ≤36 V

Ambient conditions

Ambient temperature -25 ... 60 °C (-13 ... 140 °F)

Storage temperature -40 ... 70 °C (-40 ... 158 °F)

Mechanical specifications

Degree of protection IP67

Connection 2 m fixed cable


Material

Housing PC
Optical face PMMA

Cable PVC

Mass approx. 75 g


Connection Assignment




O = Light on


= Dark on

Assembly



Characteristic Curve





Accessories

0	CPZ18B03	Mounting Bracket with swivel nut
	BF 18	Mounting flange, 18 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 190543_eng.pdf

Accessories BF 18-F Plastic mounting adapter, 18 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 \dots 30 mm