

Diffuse mode sensor, M18 threaded housing design, plastic housing, side optical face, 400 mm detection range, red light, light on, DC version, NPN output, M12 plug

Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:


· Presence checks, track loading, completeness checks, stack height control

Material handling:

- · Presence checks, target sensor, profile checks, trigger sensor
- Automatic doors, gates and access systems, elevator:
- Secure detection for automatic door and gate systems
- Monitoring function in turnstiles
- · Closing edge monitoring in elevators

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Dimensions



Technical Data

General specifications		
Detection range		50 400 mm adjustable
Detection range max.		0 400 mm
Reference target		100 mm x 100 mm Kodak white
Light source		LED
Light type		modulated visible red light , 640 nm
Diameter of the light spot		approx. 30 mm at 400 mm
Opening angle		approx. 4 °
Optical face		lateral
Ambient light limit		30000 Lux
Hysteresis	Н	< 15 %
Functional safety related parameters		
MTTF _d		920 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green, statically lit Power on
Function indicator		LED yellow: lights when object is detected ; flashes when falling short of the operating reserve
Control elements		sensitivity adjustment
Electrical specifications		
Operating voltage	U _B	10 30 V DC
No-load supply current	I ₀	< 20 mA
Output		


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 190544_eng.pdf

GLV18-8-400-S/25/102/159

Technical Data		
Switching type		light-on
Signal output		1 NPN, short-circuit protected open collector
Switching voltage		max. 30 V DC
		max. 30 v DC
Switching current		≤ 1.5 V DC
Voltage drop	U _d	
Switching frequency	f	500 Hz
Response time		≤1 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
Protection class		II, Rated insulation voltage \leq 50 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		cULus Listed, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 60 °C (-13 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		3-pin, M12 x 1 connector
Material		
Housing		PC
Optical face		PMMA
Connector		plastic
Mass		approx. 10 g

Connection Assignment



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 190544_eng.pdf

Diffuse mode sensor


Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
3	BU	(blue)
4	BK	(black)

Assembly



Characteristic Curve




Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 190544_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

4

Characteristic Curve



Accessories

0	CPZ18B03	Mounting Bracket with swivel nut
	BF 18	Mounting flange, 18 mm
	BF 18-F	Plastic mounting adapter, 18 mm
00	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
ø /	V11-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 3-pin, PUR cable grey

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

5