


# Ultrasonic sensor UB120-12GM-I-V1

- Extremely narrow projection coneAnalog output 4 mA ... 20 mA
- Very small unusable area
- Measuring window adjustable
- Short response time

Single head system



# **Dimensions**




# **Technical Data**

General specifications	
Sensing range	15 120 mm
Adjustment range	20 120 mm
Dead band	0 15 mm
Standard target plate	10 mm x 10 mm
Transducer frequency	approx. 850 kHz
Response delay	approx. 27 ms
Indicators/operating means	
LED yellow	solid yellow: object in the evaluation range yellow, flashing: program function, object detected

#### Technical Data LED red solid red: Error red, flashing: program function, object not detected **Electrical specifications** 10 ... 30 V DC , ripple 10 %SS Operating voltage $U_{\mathsf{B}}$ No-load supply current $I_0$ ≤ 30 mA Input Input type 1 program input lower evaluation limit A1: -U<sub>B</sub> ... +1 V, upper evaluation limit A2: +4 V ... +U<sub>B</sub> input impedance: > $4.7 \text{ k}\Omega$ , pulse duration: $\geq 1 \text{ s}$ Output Output type 1 analog output 4 ... 20 mA Resolution 0.17 mm Deviation of the characteristic curve ± 1 % of full-scale value ± 0.5 % of full-scale value Repeat accuracy Load impedance 0 ... 300 Ohm Temperature influence ± 1.5 % of full-scale value Compliance with standards and directives Standard conformity Standards EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 EN 60947-5-7:2003 IEC 60947-5-7:2003 Approvals and certificates cULus Listed, Class 2 Power Source **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) Mechanical specifications Connection type Connector plug M12 x 1 , 4-pin Housing diameter 12 mm Degree of protection IP67 Material Housing brass, nickel-plated Transducer epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT Mass 25 g

### Connection

Standard symbol/Connections: (version I)



Core colours in accordance with EN 60947-5-2.

Ultrasonic sensor UB120-12GM-I-V1

# **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)


# **Characteristic Curve**

## Characteristic response curve



Curve 1: flat surface 10 mm x 10 mm Curve 2: round bar, Ø 8 mm

### Programming the analog output mode



# **Programming**

Adjusting the evaluation limits

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage -UB or +UB to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with -UB, A2 with +UB. Five different output functions can be set:

1. Window mode, normally-open function

- 2. Window mode, normally-closed function
- 3. One switching point, normally-open function
- 4. One switching point, normally-closed function



Ultrasonic sensor UB120-12GM-I-V1

## **Programming**

#### 5. Detection of object presence

### TEACH-IN window mode, normally-open function

- · Set target to near switching point
- TEACH-IN switching point A1 with -UB
- · Set target to far switching point
- · TEACH-IN switching point A2 with +UB

#### TEACH-IN window mode, normally-closed function

- · Set target to near switching point
- TEACH-IN switching point A2 with +UB
- · Set target to far switching point
- TEACH-IN switching point A1 with -UB

# **TEACH-IN switching point, normally-open function**• Set target to near switching point

- TEACH-IN switching point A2 with +UB
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB

#### TEACH-IN switching point, normally-closed function

- · Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A2 with +UB

# TEACH-IN detection of objects presence

- · Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB
- TEACH-IN switching point A2 with +UB

#### **LED Displays**

Displays in dependence on operating mod	Red LED	Yellow LED
TEACH-IN switching point: Object detected No object detected Object uncertain (TEACH-IN invalid)	off flashes on	flashes off off
Normal operation	off	Switching state
Fault	on	Previous state

## **Accessories**

21	UB-PROG2	Programming unit
300	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
	BF 12	Mounting flange, 12 mm
	BF 12-F	Plastic mounting adapter, 12 mm
6/	V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey
61	V1-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey
an a	UVW90-M12	Ultrasonic -deflector
00	M12K-VE	Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors

# **Additional Information**

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF 12, BF 12-F or BF 5-30 must be used. In case of direct mounting of the sensor in a through hole, it has to be fixed at the middle of the housing thread.