

Thru-beam sensor, M18 threaded housing design, plastic housing, front optical face, 20 m detection range, red light, dark on, DC version, NPN output, fixed cable

Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control


Material handling:

- · Presence checks, target sensor, profile checks, trigger sensor
- Automatic doors, gates and access systems, elevator:
- Secure detection for automatic door and gate systems
- Monitoring function in turnstiles
- Closing edge monitoring in elevators

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Dimensions



15



Technical Data

System componentsEmitterGD18/115ReceiverGV18/59/102/115General specificationsEffective detection range0 20 mThreshold detection range25 mLight sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
ReceiverGV18/59/102/115General specifications0 20 mEffective detection range0 20 mThreshold detection range25 mLight sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
General specificationsEffective detection range0 20 mThreshold detection range25 mLight sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
Effective detection range0 20 mThreshold detection range25 mLight sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
Threshold detection range25 mLight sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
Light sourceLEDLight typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
Light typemodulated visible red light , 640 nmDiameter of the light spotapprox. 1300 mm at 25 mOpening angleapprox. 3 °Optical facefrontalAmbient light limit30000 Lux	
Diameter of the light spot approx. 1300 mm at 25 m Opening angle approx. 3 ° Optical face frontal Ambient light limit 30000 Lux	
Opening angle approx. 3 ° Optical face frontal Ambient light limit 30000 Lux	
Optical face frontal Ambient light limit 30000 Lux	
Ambient light limit 30000 Lux	
Functional safety related parameters	
i unchonai salety related paralliciers	
MTTF _d 630 a	
Mission Time (T _M) 20 a	
Diagnostic Coverage (DC) 0 %	
Indicators/operating means	
Operation indicator LED green, statically lit Power on	
Function indicator Receiver: LED yellow, lights up when light beam is free, flashes when falling the operating reserve; OFF when light beam is interrupted	short of
Electrical specifications	
Operating voltage U _B 10 30 V DC	

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 188548_eng.pdf

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com





2

GD18/GV18/59/102/115

Technical Data		
No-load supply current	I ₀	< 20 mA
Output	10	
Switching type		dark-on
Signal output		1 NPN, short-circuit protected open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U_d	≤ 1.5 V DC
Switching frequency	f	500 Hz
Response time		≤ 1 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
Protection class		II, Rated insulation voltage \leq 50 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		cULus Listed, Class 2 Power Source, Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 60 °C (-13 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		PC
Optical face		PMMA
Mass		approx. 75 g per device

Connection Assignment






O = Light on $\bullet = Dark on$

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Pepperl+Fuchs Group www.pepperl-fuchs.com

Assembly



1	Operating display	green
2	Signal display	yellow
4	Emitter	
5	Receiver	

Characteristic Curve



Accessories

CPZ18B03

Mounting Bracket with swivel nut



Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 188548_eng.pdf

BF 18

Mounting flange, 18 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

4

Acces	ssories	
54	BF 18-F	Plastic mounting adapter, 18 mm
000	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

5