

Safety control unit SB4-OR-4XP



- Evaluation unit for security through-beam sensors SLA5(S) and SLA40; for safety light grids SLP, for safety light curtains SLC; for switching pads and emergency stop buttons of categories 2 and 4
- 4 sensor channels
- Self-monitoring (type 4 according to IEC/EN 61496-1)
- Operating mode can be selected by means of DIP switches
- Start/Restart disable
- Relay monitor
- Stability alarm indication
- Clearly visible LED functional display
- 7-segment diagnostic display
- Safety outputs OSSD, external status displays OSSD


Safety control unit










Dimensions









Technical Data

General specifications	
Operating mode	Start/restart disable, relay monitor,
Functional safety related parameters	
Safety Integrity Level (SIL)	SIL 3
Performance level (PL)	PL e
Category	Cat. 4
Mission Time (T _M)	20 a
PFH _d	3.5 E-9

www.pepperl-fuchs.com



Technical Data B_{10d} see instruction manuals Type Indicators/operating means Diagnostics indicator 7-segment display Function indicator LED red: OSSD OFF LED green: OSSD ON Yellow LED: start readiness channel 1 - 4 LED yellow: switching state (receiver) Stability alarm indicator LED yellow flashing: Indicator lamp channel 1 ... 4 **Electrical specifications** Operating voltage U_{B} 24 V DC, \pm 20 % I_0 No-load supply current max. 500 mA Protection class no identification; see instruction manuals Input Activation current approx. 7 mA Activation time 0.4 ... 1.2 s Test input Reset-input for system test Output Safety output 2 relay outputs, force-guided NO-contact Output for displaying the switching state of the OSSDs Signal output 10 V ... 250 V AC/DC Switching voltage Switching current min. 10 mA, max. 6 A AC/DC Switching power DC: max. 24 VA AC: max. 230 VA Response time 30 ms Conformity Functional safety ISO 13849-1; EN 61508 part1-4 Product standard EN 61496-1 Approvals and certificates CE conformity CE **UKCA** conformity **UKCA** cULus **UL** approval ΤÜV TÜV approval **Ambient conditions** Ambient temperature 0 ... 50 °C (32 ... 122 °F) Storage temperature -20 ... 70 °C (-4 ... 158 °F) max. 95 %, not condensing Relative humidity Shock resistance see instruction manuals Vibration resistance see instruction manuals Mechanical specifications Degree of protection IP20 Connection screw terminals, lead cross section 0.2 ... 2 mm2 Material Housing Polyamide (PA) Mass 320 g



Safety control unit SB4-OR-4XP

Connection

0000	0000
0000	0000
13 14 15 16 9 10 11 12 \$\frac{1}{2} OSSD	13 14 15 16 9 10 11 12 -X+R4
‡ RI	.‡ R3
8.	☆R2 ☆R1
1 2 3 4 5 6 7 8	1 2 3 4 5 6 7 8
0000	0000
0000	0000

Slot 1 Slot 2

Terminal Slot 1

Terminal	Function
1	Reset input; normally closed contact
2	Restart input (RI); normally closed contact
3	24 V DC connection for reset, restart and RM
4	Relay monitor (RM)
5 - 6	OSSD1; potential free relay contact; normally open contact
7 - 8	OSSD2; potential free relay contact; normally open contact
9	Signal output OSSD OFF
10	Signal output OSSD ON
11	Signal output restart
12	Leave free (n.c.)
13	+24 V DC supply voltage
14	0 V DC supply voltage
15	Earth
16	Leave free (n.c.)

Terminal Slot 2

Terminal	Function	Channel	Connection	Connection 2-channel	Connection
		classification	Beam sensor / Light grid safety feature	p ON	Switching pad
1	Receiver 2 Input	Input	Receiver output 2	OSSD Output 1.2	Switching pad 1.4
2	Sensor 2 24 V DC +U	Channel 2	24 V Receiver2	24 V Power supply 1	
3	Sensor 2 Mass GND		0 V Receiver 2, Emitter 2	0 V Power supply 1	
4	Emitter 2 Output	Output	Emitter input 2		Switching pad 1.3
5	Receiver 1 Input	Input	Receiver output 1	OSSD Output 1.1	Switching pad 1.2
6	Sensor 1 24 V DC +U	Channel 1	24 V Receiver 1		
7	Sensor 1 Mass GND		0 V Receiver 1, Emitter 1		
8	Emitter 1 Output	Output	Emitter input 1		Switching pad 1.1
9	Emitter 3 Output	Output	Emitter input 3		Switching pad 2.4
10	Sensor 3 Mass GND	Channel 3	0 V Receiver 3, Emitter 3	0 V Power supply 2	
11	Sensor 3 24 V DC +U		24 V Receiver 3	24 V Power supply 2	
12	Receiver 3 Input	Input	Receiver output 3	OSSD Output 2.2	Switching pad 2.3
13	Emitter 4 Output	Output	Emitter input 2		Switching pad 2.2
14	Sensor 4 Mass GND	Channel 4	0 V Receiver 4, Emitter 4		
15	Sensor 4 24 V DC +U		24 V Receiver 4		
16	Receiver 4 Input	Input	Receiver output 4	OSSD Output 2.1	Switching pad 2.1

Matching System Components



Matching System Components

	SLP10-4	Safety light grid
	SLP10-4-L	Safety light grid
	SLCT14	Safety light curtain
	SLCT14-*-3702	Safety light curtain
	SLCT30	Safety light curtain
	SLCT30-/35	Safety light curtain
Î	SLCT30-*-3702	Safety light curtain
	SLCT60	Safety light curtain
	SLCT60-/35	Safety light curtain
	SLCT90	Safety light curtain
	SLCT90-/35	Safety light curtain
	SLCS14	Safety light curtain
	SLCS14-*-3702	Safety light curtain
	SLCS14-*-3702	Safety light curtain
	SLCS30	Safety light curtain
	SLCS30/35	Safety light curtain
	SLCS30-*-3702	Safety light curtain
	SLCS30-*-3702	Safety light curtain
	SLCS60	Safety light curtain
	SLCS60/35	Safety light curtain

SB4-OR-4XP

Matching System Components

SLCS90	Safety light curtain
SLCS90/35	Safety light curtain
SLCT-M-01	Inclined mirror for stable 90° deflection with cover plate
SLCT-M-01-1200	Inclined mirror for stable 90° deflection with cover plate
SLCT-M-01-1500	Inclined mirror for stable 90° deflection with cover plate
SLCT-M-01-2100	Inclined mirror for stable 90° deflection with cover plate
SLC-XXX-M	Safety light grid mirror

Function

The evaluation system SB4 is an ESPE of type 4 (EN 61496-1 or IEC 61496-1) or category 4 (EN 954-1). This system is also designed and tested according to IEC 61508. It meets the requirements for the SIL3.

The operating instructions supplied with the device must be observed for planning, installation and operation.

A maximum of 4 safety light barriers can be connected to the evaluation device.

With the sensor card on position 2, it is possible to connect "3-wire" light barriers of the SLA family (for example SLA5) and light grids of the SLP type. But also p-switching safety devices with dedicated cross circuit monitoring can be connected, for example safety light curtains from the SLC family. In addition switch-off mats of the 4-wire principle or integrated safety sensors in the 1 or 2 channel version can be connected.

The cable or the manner it is laid to the light barriers and light grids must be chosen that no short circuit between the receiver and transmitter wires is possible.

Light curtains with semiconductor switch outputs and integrated safety sensors in 2 channel design are monitored for simultaneousness. The monitoring time is 2 s.

The connection is done on channels 3 and 4 and/or 1 and 2. Note that these sensors must feature a dedicated cross circuit monitoring, because the module does not

carry out the cross circuit monitoring for these sensors. Integrated safety sensors, which are connected to the Safebox must work according to the normally closed principle.

An open contact means "safe status". Switch-off mats of the 4-wire principle can be connected to channels 1 and 2 and/or 3 and 4.

Operating modes

By default, the restart interlock is activated.

Each assembly contains DIP switches for selecting the functions. For selecting functions, 2 selector switches must always be actuated.

Switches on the first assembly:

Switch	Position	Operating mode
1 and 3	OFF	Without restart interlock (restart, RI)
	ON	With restart interlock (restart, RI)
2 and 4	OFF	Without relay monitor (RM)
	ON	With relay monitor (RM)

Switches on the second assembly:

The assembly contains 6 DIP switches for selecting the sensor types and the position. Six possibilities are offered for combining sensors. The desired combination is to be set binary. Two switches must always be actuated in order to select a function, e.g. DIP switches 1-3 have the same switch position as DIP switches 4-6.

DIP switch			Operating mode
3 and 6	2 and 5	1 and 4	
0	0	0	SLA /SLP/bridge channel 1 + 2 and channel 3 + 4
0	0	1	SLA /SLP/bridge on channel 1 + 2 and SLC channel 3 + 4
0	1	0	SLC channel 1 + 2 and channel 3 + 4
0	1	1	SLA /SLP/bridge channel 1 + 2 and safety mat channel 3 + 4
1	0	0	Safety mat channel 1 + 2 and channel 3 + 4
1	0	1	SLC channel 1 + 2 and safety mat channel 3 + 4

Displays

The OSSD-R/supply module on position 1 has a red/green LED for indicating the OSSD on/off statuses, a yellow LED for the startready status and a 7 segment display for system diagnosis.

The 7 segment display indicates the status and the error codes of the system.

Displ ay	7 segment display
1	DIP switch positions differ
2	Incorrect configuration
3	Time-out at one or more muting sensors
4	Transmitter error
6	Muting lamp error
7	Simultaneousness monitoring error

8	Receiver error
9	Error at sensor channel
С	Error at sensor channel
E	System error
F	Relay monitor error
Н	Selection chain error
L	Configuration error
U	Low voltage or voltage surge detected

SB4-OR-4XP