

Retroreflective sensor

ML9-54-G/25/136/143





- Ultra bright LEDs for power on, weak signal indication and switching state
- Flashing power on LED in case of short-circuit
- **TEACH-IN**
- Automatic adjustment in case of soiling in contrast detection
- Not sensitive to ambient light, even with switched energy saving
- Protected against mutual interference (no cross-talk)
- Protection class II

Retroreflective sensor with polarization filter for clear object detection



Dimensions








Technical Data

| General specifications | | |
|---------------------------|---|--|
| Effective detection range | 0 3.5 m in TEACH mode 0 5.7 m in normal mode | |
| Reflector distance | 0 3.5 m in TEACH mode 0 5.7 mm in normal mode | |
| Threshold detection range | 7.6 m | |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

| Technical Data | | |
|--------------------------------------|----------------|--|
| Reference target | | H85-2 reflector |
| Light source | | LED |
| Light type | | modulated visible red light , 660 nm |
| Polarization filter | | yes |
| Angle deviation | | max. ± 1° |
| Diameter of the light spot | | approx. 40 mm at detection range 1 m |
| Opening angle | | 1.7° |
| Ambient light limit | | 40000 Lux |
| Functional safety related parameters | | |
| MTTF _d | | 1050 a |
| Mission Time (T _M) | | 20 a |
| Diagnostic Coverage (DC) | | 0% |
| Indicators/operating means | | 7 / 0 |
| Operation indicator | | LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) |
| Function indicator | | LED yellow: switching state; Stability control; Teach-In |
| Control elements | | Teach-In key |
| Contrast detection levels | | 10 % - clean, water filled PET bottles |
| Electrical specifications | | |
| Operating voltage | U _B | 10 30 V DC , class 2 |
| Ripple | - 5 | max. 10 % |
| No-load supply current | I ₀ | < 20 mA at 24 V DC |
| Output | -0 | |
| Switching type | | light-on |
| Signal output | | 2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 100 mA |
| Switching frequency | f | 1000 Hz |
| Response time | | 500 μs |
| Conformity | | |
| Product standard | | EN 60947-5-2 |
| Approvals and certificates | | |
| EAC conformity | | TR CU 020/2011 |
| Protection class | | II, rated voltage ≤ 50 V AC with pollution degree 1-2 according to IEC 60664-1 functional insulation acc. to DIN EN 50178 |
| UL approval | | cULus |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | |
| Ambient temperature | | -20 60 °C (-4 140 °F) |
| Storage temperature | | -40 75 °C (-40 167 °F) |
| Mechanical specifications | | |
| Housing width | | 23 mm |
| Housing height | | 38 mm |
| Housing depth | | 11 mm |
| Degree of protection | | IP67 |
| Connection | | M8 x 1 connector, 4-pin |
| Material | | |
| Housing | | PC (glass-fiber-reinforced Makrolon) |
| Optical face | | glass |
| Connector | | plastic |
| Mass | | approx. 25 g |

Connection



- O = Light on
- = Dark on


Connection Assignment




Wire colors in accordance with EN 60947-5-2


1 BN (brown) 2 WH (white) 3 BU (blue) 4 BK (black)

Assembly



| 1 | LED green |
|---|------------|
| 2 | LED yellow |
| 3 | Teach-In |





Accessories

| | OMH-ML9 | Mounting aid for ML9 series, Mounting bracket |
|---|---------------|--|
| | | |
| | OMH-ML9-01 | Mounting aid for ML9 series, Threaded bolt M3 |
| 2 | V31-GM-2M-PVC | Female cordset single-ended M8 straight A-coded, 4-pin, PVC cable grey |
| | V31-WM-2M-PVC | Female cordset single-ended M8 angled A-coded, 4-pin, PVC cable grey |
| 2 | V31-GM-5M-PUR | Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey |
| | V31-WM-5M-PUR | Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey |

Adjustment instructions for devices with Teach-In

After the operating voltage has been applied, the LED is lit green. The sensor is automatically set to a state of maximum sensitivity (state as supplied) or the state of the most recent Teach-In setting.

Assemble the appropriate reflector opposite the light barrier.

Teach-In using the Teach key

- · Align the sensor to an appropriate reflector.
- Press the Teach key as confirmation, the green display LED is briefly turned off once.
- Hold the Teach key down until the yellow and green display LED is flashing at regular intervals (about 2.5 Hz).
 Then release the Teach key.
- During the internal set-up of the sensor, the green and yellow display LEDs flash alternately (about 2.5 Hz).
- Teach-In successful: The green and yellow display LEDs are lit. Contrast detection 10% is activated. The device is ready for operation.
- Teach-In not successful: The green and yellow display LEDs flash alternately and rapidly (about 8 Hz) for about 5 seconds. Then the sensor goes to the state with maximum sensitivity.
 - After this happens, repeat the Teach-In procedure, starting with step 1.