Photoelectric slot sensor



Model Number

Features

•

•

•

GL220-LAS/32/40a/98a

Photoelectric slot sensor with 3-pin, M8 x 1 connector

High resolution

High switching frequency

Sturdy aluminum housing

Light/dark switching

Alignable housing Adjustable sensitivity


Product information

Photoelectric slot sensors with laser light can


be used in applications with specific, demanding requirements and are ideal for

highly precise and extremely fast applications. These eye-safe laser devices stand out through attributes that include particularly high switching frequencies of 10 kHz, maximum repeatability of 0.01 mm, automatic signal threshold adjustment, and detection of and/or light transmission through semi-transparent objects. In addition, the devices fea-

ture cross-talk protection, which enables devices to be installed adjacent to each other despite very high switching frequency.



Electrical connection




= Dark on

Pinout



Indicators/operating means



1	Functional display	yellow	
2	Sensitivity adjuster		
3	Light-/dark switch		

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical	data
recimical	uata

Technical data					
General specifications					
Light source		laser diode			
Light type		red			
Laser nominal ratings					
Note		LASER LIGHT , DO NOT STARE INTO BEAM			
Laser class		2			
Wave length		650 nm			
Beam divergence		2.6 mrad			
Maximum optical power output		< 1 mW			
Target size		0.05 mm			
Fork width		220 mm			
Ambient light limit		10000 Lux			
Hysteresis	н	< 0.02 mm			
Indicators/operating means					
Function display		LED yellow 4 x			
Controls		Sensitivity adjuster, light/dark switch			
Electrical specifications					
Operating voltage	U _B	10 30 V DC			
No-load supply current	I ₀	45 mA			
Output	·U	-			
Switching type		light/dark on			
Signal output		1 PNP output, short-circuit protected, reverse polarity protected,			
Cigital output		open collector			
Switching voltage		max. 30 V DC			
Switching current		max. 200 mA			
Voltage drop	Ud	2.5 V (200 mA)			
Switching frequency	f	10000 Hz			
Response time		50 µs			
Ambient conditions					
Ambient temperature		-10 60 °C (14 140 °F)			
Mechanical specifications					
Protection degree		IP65			
Connection		M8 connector, 3-pin			
Material					
Housing		black anodized aluminum			
Optical face		glass			
Installation		may be mounted in rows			
Mass		30 g			
Compliance with standards and	directi	-			
ves	anoon				
Directive conformity		EMC Directive 2004/108/EC			
Standard conformity					
Product standard		EN 60947-5-2:2007			
		IEC 60947-5-2:2007			
Laser class		IEC 60825-1:2007			
Approvals and certificates					
CCC approval		CCC approval / marking not required for products rated ${\leq}36~\text{V}$			
Laser notice laser class	2				
		tion conscielly in a dark onvironment. Do not point			
• The irradiation can lead to irritation especially in a dark environment. Do not point					
at people!					
Caution: Do not look into the beam!					
Maintenance and repairs should only be carried out by authorized service person-					
nel!					
 Attach the device so that the warning is clearly visible and readable. 					
Caution – Use of controls or adjustments or performance of procedures other than					
		It in hazardous radiation exposure.			
·	-	·			

Laserlabel



Accessories

V3-GM-2M-PUR Cable socket, M8, 3-pin, PUR cable

V3-WM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

PEPPERL+FUCHS

Singapore: +65 6779 9091

fa-info@sg.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

fa-info@de.pepperl-fuchs.com

www.pepperl-fuchs.com