


Retroreflective sensor with polarization filter for clear object detection

Dimensions



Technical Data

| General specifications | | |
|---------------------------|--|--|
| Effective detection range | 0 3.5 m in TEACH mode 0 5.7 m in normal mode | |
| Reflector distance | 0 3.5 m in TEACH mode 0 5.7 mm in normal mode | |
| Threshold detection range | 7.6 m | |
| | | |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



ML9-54-G/102/115/126b


| Technical Data | | |
|--------------------------------------|----------------|--|
| Reference target | | H85-2 reflector |
| Light source | | LED |
| Light type | | modulated visible red light , 660 nm |
| Polarization filter | | yes |
| Angle deviation | | max. $\pm 1^{\circ}$ |
| Diameter of the light spot | | approx. 40 mm at detection range 1 m |
| Opening angle | | 1.7° |
| Ambient light limit | | 40000 Lux |
| Functional safety related parameters | | |
| MTTF _d | | 1050 a |
| Mission Time (T _M) | | 20 a |
| Diagnostic Coverage (DC) | | 0% |
| Indicators/operating means | | 0 70 |
| Operation indicator | | LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing |
| | | (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) |
| Function indicator | | LED yellow: switching state ; Stability control ; Teach-In |
| Control elements | | Teach-In key |
| Contrast detection levels | | 10 % - clean, water filled PET bottles |
| Electrical specifications | | |
| Operating voltage | U _B | 10 30 V DC , class 2 |
| Ripple | | max. 10 % |
| No-load supply current | I ₀ | < 20 mA at 24 V DC |
| Output | | |
| Pre-fault indication output | | 1 NPN function reserve output (alarm), short-circuit protected, reverse polarity protected, open collector |
| Switching type | | dark-on |
| Signal output | | 1 NPN output, short-circuit protected, reverse polarity protected, open collector |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 100 mA |
| Switching frequency | f | 1000 Hz |
| Response time | | 500 μs |
| Conformity | | |
| Product standard | | EN 60947-5-2 |
| Approvals and certificates | | |
| EAC conformity | | TR CU 020/2011 |
| Protection class | | II, rated voltage \leq 50 V AC with pollution degree 1-2 according to IEC 60664-1 functional insulation acc. to DIN EN 50178 |
| UL approval | | cULus |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | |
| Ambient temperature | | -20 60 °C (-4 140 °F) |
| Storage temperature | | -40 75 °C (-40 167 °F) |
| Mechanical specifications | | |
| Housing width | | 23 mm |
| Housing height | | 38 mm |
| Housing depth | | 11 mm |
| Degree of protection | | IP67 |
| Connection | | 2 m fixed cable |
| Material | | |
| Housing | | PC (glass-fiber-reinforced Makrolon) |
| Optical face | | glass |
| Mass | | approx. 25 g |
| Muoo | | uppion to g |

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com


Connection Assignment




O = Light on

• = Dark on

Assembly



Characteristic Curve




Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Retroreflective sensor

Characteristic Curve



Pepperl+Fuchs Group www.pepperl-fuchs.com fa-i

Release date: 2022-08-02 Date of issue: 2022-08-03 Filename: 194198_eng.pdf

4

Adjustment instructions

Adjustment instructions for devices with Teach-In

After the operating voltage has been applied, the LED is lit green. The sensor is automatically set to a state of maximum sensitivity (state as supplied) or the state of the most recent Teach-In setting.

Assemble the appropriate reflector opposite the light barrier.

Teach-In using the Teach key

- Align the sensor to an appropriate reflector.
- Press the Teach key as confirmation, the green display LED is briefly turned off once.
- Hold the Teach key down until the yellow and green display LED is flashing at regular intervals (about 2.5 Hz). Then release the Teach key.
- During the internal set-up of the sensor, the green and yellow display LEDs flash alternately (about 2.5 Hz).
- Teach-In successful: The green and yellow display LEDs are lit. Contrast detection 10% is activated.
- The device is ready for operation.
- Teach-In not successful: The green and yellow display LEDs flash alternately and rapidly (about 8 Hz) for about 5 seconds. Then the sensor goes to the state with maximum sensitivity.
 After this happens, repeat the Teach-In procedure, starting with step 1.

Release date: 2022-08-02 Date of issue: 2022-08-03 Filename: 194198_eng.pdf

