

DeviceNet Gateway, double master for 2 AS-Interface networks



# **Function**


The VBG-DN-K20-DMD is a DeviceNet gateway with two AS-Interface masters compliant with AS-Interface specification 3.0. The variant in an IP20 stainless steel housing is particularly suitable for use in the switching cabinet for snapping onto 35mm mounting rails. The gateway is a 100% DeviceNet slave (group 2 slave) and, as a listed product, directly addressable through the DeviceNet device manager. Communication between the ASInterface and DeviceNet is implemented by the gateway with no additional programming effort. For the AS-Interface gateway with graphic display, the commissioning of the AS-Interface circuit as well as the test of the connected periphery can be completely as the gateway with gate the gateway display and display and as the second display.


For the AS-interface gateway with graphic display, the commissioning of the AS-interface circuit as well as the test of the connected periphery can be completely separated from the commissioning of the DeviceNet as well as the programming. On-site operation using the graphical display and the four buttons make it possible to perform all functions on the display. Address assignment and transfer of the expected configuration can be done with the buttons. There are 7 LEDs on the front panel, showing the current status of the AS-i line. An additional RS 232 socket is available with the option to read out data directly from the gateway via gateway, network and function within the scope of an enhanced on-site diagnosis. Using the AS-i Control Tools package (not included), many functions can be remotely controlled via PC. The gateway draws its power from the AS-interface cable. The connection of the AS-interface gateway to the DeviceNet uses the 5pin CombiCon

plug according to the DeviceNet specification. There are self-opening device terminals available for all other connections. PLC Functionality

Furthermore, the gateway can optionally be delivered with PLC functionality. Therefor you can order a code key VAZ-CTR additionally.

#### **Dimensions**





# **Technical Data**

General specifications		
AS-Interface specification	V3.0	
PLC-Functionality	activateable	
Duplicate address detection	from AS-Interface slaves	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



# AS-Interface gateway

## **Technical Data**

## VBG-DN-K20-DMD

Technical Data		
Earth fault detection	EFD	integrated
EMC monitoring		integrated
Diagnostics function		Extended function via display
UL File Number		E223772 only from low voltage, limited energy source (SELV or PELV) or listed Class 2 source
Indicators/operating means		
Display		Illuminated graphical LC display for addressing and error messages
LED AS-i ACTIVE		AS-Interface operation normal; LED green
LED CONFIG ERR		configuration error; LED red
LED PRG ENABLE		autom. programming; LED green
LED POWER		voltage ON; LED green
LED PRJ MODE		projecting mode active; LED yellow
LED U AS-i		AS-Interface voltage; LED green
LED MNS		Module/net status; LED green/red
Switch SET		Selection and setting of a slave address
OK button		Mode selection traditional-graphical/confirmation
Button MODE		Mode selection PRJ-operation/save configuration/cursor
ESC button		Mode selection traditional-graphical/cancel
Electrical specifications		
Insulation voltage	Ui	≥ 500 V
Rated operating voltage	Ue	from AS-Interface
Rated operating current	l <sub>e</sub>	≤ 200 mA from AS-Interface circuit 1 ≤ 70 mA from AS-Interface segment 2
Interface 1		
Protocol		DeviceNet
Interface 2		
Interface type		RS 232, serial Diagnostic Interface
Transfer rate		19,2 kBit/s
Connection		
AS-Interface		spring terminals, removable
DeviceNet		5-pin CombiCon connector according to DeviceNet specification
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 62026-2:2013
Standard conformity		
Electromagnetic compatibility		EN 61000-6-2:2005, EN 61000-6-4:2001, EN 50295:1999
Degree of protection		EN 60529:2000
AS-Interface		EN 62026-2:2013
Shock resistance		EN 61131-2
Approvals and certificates		
UL approval		An isolated source with a secondary open circuit voltage of $\leq 30 V_{DC}$ with a 3 A maximum over current protection. Over current protection is not required when a Clas 2 source is employed. UL mark does not provide UL certification for any functional safety rating or aspects of the device.
Ambient conditions		
Ambient temperature		0 55 °C (32 131 °F)
Storage temperature		-25 85 °C (-13 185 °F)
• •		
Mechanical specifications Degree of protection		IP20
Mechanical specifications		IP20 520 g

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

#### Connection



At the cable for power supply no slaves or repeaters may be attached. At the cable for AS-Interface circuit no power supplies or further masters may be attached.

## Assembly



Release date: 2022-12-15 Date of issue: 2022-12-15 Filename: 190325\_eng.pdf


C

1

Accessories

O los	VAZ-SW-ACT32	Full version of the AS-I Control Tools including connection cable
	USB-0,8M-PVC ABG- SUBD9	Interface converter USB/RS 232

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



#### Connection

In an AS-Interface network only one device can be operated earth fault detection. If there are many devices in an AS-Interface network, this can lead to the earth fault monitoring response threshold becoming less sensitive.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

4