

Print mark contrast sensor DK12-11/A/124/136



- Diffuse mode sensor for recording any print mark
- TEACH-IN, static and dynamic
- 50 µs response time, suitable for extremely rapid scanning processes
- 3 emitter colors: green, red and blue

Print mark contrast sensor, 11 mm detection range, RGB light perpendicular to the longitudinal direction of the housing, light/dark ON, external Teach-In, 2 push-pull outputs, M12 plug



Dimensions



Technical Data

General specifications

Sensor range

11 mm ± 2 mm

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 G

Pepperl+Fuchs Group US www.pepperl-fuchs.com fa-info@



1

Technical Data

DK12-11/A/124/136

Light source		3 LEDs (R.G.B)	
Light type		Visible green/red/blue, modulated light	
Light spot representation		3 mm x 1 mm light spot perpendicular to bousing	
Angle deviation		max. ± 3°	
Teach-In		static and dynamic Teach-In	
Functional safety related parameters			
MTTEd		750 a	
Mission Time (T _M)		20 a	
Diagnostic Coverage (DC)		60 %	
Indicators/operating means			
Operation indicator		LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz)	
Function indicator		2 LEDs yellow, light up in case of detection	
Teach-In indicator		Teach-In mark: LED green/yellow equiphase flashing; 2,5 Hz . Teach-In background: LED green/yellow non equiphase flashing; 2,5 Hz . Teach-In dynamic: LED green/yellow equiphase flashing; 1.0 Hz . Teach Error:LED green/yellow non equiphase flashing; 8.0 Hz .	
Control elements		Teach-In rotary switch for Switching operation, Teach-In mark, Teach-In background and dynamic Teach-In	
Electrical specifications			
Operating voltage	UB	10 30 V DC	
Ripple		10 %	
No-load supply current	I ₀	≤ 80 mA	
Input			
Function input		Ext. Teach-In input (ET)	
Output			
Switching type		light/dark on	
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Switching frequency	f	10 kHz	
Response time		50 µs	
Conformity			
Product standard		EN 60947-5-2	
Approvals and certificates			
Protection class		II, rated voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1	
UL approval		cULus Listed, Class 2 power source	
CCC approval		CCC approval / marking not required for products rated \leq 36 V	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-40 75 °C (-40 167 °F)	
Mechanical specifications			
Housing width		41.5 mm	
Housing height		49 mm	
Housing depth		15 mm	
Degree of protection		IP67	
Connection		Metal connector, M12, 5-pin, 90° rotatable	
Material			
Housing		Frame: nickel plated, die cast zinc, Laterals: glass-fiber reinforced plastic PC	
Optical face		Plastic pane	
Mass		60 g	

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Connection Assignment



O = Backround

= Mark

Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

Assembly



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com fi

F PEPPERL+FUCHS

DK12-11/A/124/136



Teach-In

If the object surfaces are reflective or shiny, tilt the sensor approximately 10° toward the surface of the material.

- Teach-in via rotary switch: Teach-in via rotary switch is possible in four positions. TM position: Teach-in mark
- TB position: Teach-in background
- TD position: Teach-in dynamic
- S position: Switching mode ٠

To change the switch position, a time lock of approximately 1 second must be adhered to in each case. This means that the rotary switch must remain in a new position constantly for 1 second in order for the sensor to accept the required mode. The mode can be identified by the how the flashing function of the signal indicators changes.

Static teach-in (TM/TB): The mark or the background can be taught-in in static teach-in mode, either together (in any order) or separately.

- Therefore it is not mandatory to always teach-in the mark and the background.
 TM position: The teach-in procedure starts. Continuous value transfer takes place, and the color of the scanned object can be changed. When leaving TM position, the sensor assumes the last value. In "teach-in mark" mode, the green and yellow signal indicators flash simultaneously at f = 2.5 Hz.
- TB position: Same functionality as in TM position. In "teach-in background" mode, the green and yellow signal indicators flash alternately at f = 2.5 Hz.

Teach-in dynamic (TD/S)

- **TD position:** The teach-in process starts. Continuous value transfer takes place, and the sensor interprets the first recorded signals as a background after entering "dynamic teach-in" mode. For the duration of "dynamic teach-in" mode, the sensor indicates the greatest deviation from the background as a mark. In "teach-in dynamic" mode, the green and yellow signal indicators flash simultaneously at f = 1.0 Hz.
- S position: The current teach-in mode is terminated. The received signals of all three emitter light colors for the mark and background are evaluated.

External teach-in input: The desired operating mode can be set to switch position S by applying a high pulse with a specific width. • Teach-in dynamic (TD): 420 ms ... 450 ms

- Teach-in background (TB): 320 ms ... 350 ms
- Teach-in mark (TM): 220 ms ... 250 ms •
- Switching mode (S): 120 ms ... 150 ms

The descriptions of the individual operating modes correspond to the teach-in via rotary switch. The function of the rotary switch is deactivated during external teach-in. An external teach-in procedure must be completed with a signal to request switching mode (S).

_eng.pdf

