



Retroreflective sensor

GLK18-6-S/25/161/166



- Efficient Line in a short M18 plastic housing for standard applications
- Very high detection range
- 4 LEDs indicator for 360° visibility
- Sidelookerversion
- Universal usage at different power supplies

Retroreflective sensor, M18 threaded housing design, plastic housing, side optical face, 5.5 m detection range, red light, light on, AC/DC version, NPN-FET output, micro plug











Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control

Material handling:


· Presence checks, target sensor, profile checks, trigger sensor

Automatic doors, gates and access systems, elevator:


- Secure detection for automatic door and gate systems
- · Monitoring function in turnstiles
- · Closing edge monitoring in elevators



Dimensions









Technical Data


General specifications

Effective detection range		0 5.5 m
Reflector distance		0.05 5.5 m
Threshold detection range		6.5 m
Reference target		reflector C110-2
Light source		LED
Light type		modulated visible red light , 640 nm
Polarization filter		no
Diameter of the light spot		approx. 250 mm at 6.5 m
Opening angle		approx. 2 °
Optical face		lateral
Ambient light limit		30000 Lux
Accessories provided		Mounting aids
Indicators/operating means		
Operation indicator		LED green, statically lit Power on
Function indicator		LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted
Electrical specifications		
Operating voltage	U_B	20 250 V AC/DC
No-load supply current	I_0	< 2.5 mA
Output		
Switching type		light-on

a	
u)
_	ı
_)
σ)
\sim	
Ġ	
σ	١
-	
-	
D.	Į
_	
−	
- ``	
-	
а	J
=	
11	
_	
α	
~	
_	
_	
- 1	
O.	ı
C	4
Š	
⊼	i
	•
a	١
-	
77	۱
9,	
. U.	
- :-	
*=	
C)
-	۰
. 4	
7	1
\sim	
	١
α	
_)
4	
-	
_	
11-1	
11-1	
2-11-1	
22-11-1	
022-11-1	
22-11-1	
022-11-1	
022-11-1	
022-11-1	
022-11-1	
022-11-1	
022-11-1	
022-11-1	
date: 2022-11-1	
Please date: 2022-11-1	
Please date: 2022-11-1	
date: 2022-11-1	
Please date: 2022-11-1	
Please date: 2022-11-1	
Please date: 2022-11-1	
Please date: 2022-11-1	
Please date: 2022-11-1	

Technical Data		
Signal output		N-channel MOSFET, short circuit protected
Switching voltage		max, 250 V AC/DC
Switching current		max. 200 mA
Voltage drop	U _d	≤ 3.5 V AC/DC
Switching frequency	f	50 Hz
Response time		≤ 10 ms
Conformity		2.10 1110
Product standard		EN 60947-5-2
Compliance with standards and directives		
Standard conformity		
Standards		UL 508
Approvals and certificates		
Protection class		II, rated insulation voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		cULus Listed, Type 1 enclosure
CCC approval		Certified by China Compulsory Certification (CCC)
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Degree of protection		IP67
Connection		Micro AC connector, 1/2" V124 ; 4-pin
Material		
Housing		PC-PBT
Optical face		PMMA
Mass		approx. 10 g

Connection Assignment



O = Light on ● = Dark on


Connection Assignment




Wire colors

1 | RD/BK (red/black) 2 | RD/WH (red/white) 3 | RD (red) 4 | GN (green)


Assembly






1	_		
	1	Operating display gree	
	2	Signal display yellow	
	4	Emitter	
	5	Receiver	

Characteristic Curve





$\boldsymbol{\alpha}$	$\boldsymbol{-}$		121	
	CC	cces	ccesso	ccessori

0	CPZ18B03	Mounting Bracket with swivel nut
	BF 18	Mounting flange, 18 mm
511	BF 18-F	Plastic mounting adapter, 18 mm
100	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
	V124-G-YE2M-PVC	Connecting cable, 1/2" - 20 UNF, 4-pin, PVC cable
	V124-W-YE2M-PVC	Connecting cable, 1/2" - 20 UNF, 4-pin, PVC cable