

Retroreflective sensor GLK18-6-S/59/161/166



- Efficient Line in a short M18 plastic housing for standard applications
- Very high detection range
- 4 LEDs indicator for 360° visibility
- Sidelookerversion
- Universal usage at different power supplies

Retroreflective sensor, M18 threaded housing design, plastic housing, side optical face, 5.5 m detection range, red light, dark on, AC/DC version, NPN-FET output, micro plug











Function

The GLV/GLK18 series sensors help improve the efficiency of machines and systems. The design of the M18 plastic housing, the connection technology, and sensor properties are highly standardized. Concentrating on the key sensor requirements has produced a robust and reliable product series for DC and AC/DC voltage systems without any over-engineering. The mounting set included in the scope of delivery and the optimized potentiometer design ensure fast assembly and easy configuration.

Application

Packaging industry:

· Presence checks, track loading, completeness checks, stack height control


Material handling:

· Presence checks, target sensor, profile checks, trigger sensor


Automatic doors, gates and access systems, elevator:

- Secure detection for automatic door and gate systems
- · Monitoring function in turnstiles
- · Closing edge monitoring in elevators

Dimensions









Technical Data


General specifications

•			
Effective detection range		0 5.5 m	
Reflector distance		0.05 5.5 m	
Threshold detection range		6.5 m	
Reference target		reflector C110-2	
Light source		LED	
Light type		modulated visible red light , 640 nm	
Polarization filter		no	
Diameter of the light spot		approx. 250 mm at 6.5 m	
Opening angle		approx. 2 °	
Optical face		lateral	
Ambient light limit		30000 Lux	
Accessories provided		Mounting aids	
Indicators/operating means			
Operation indicator		LED green, statically lit Power on	
Function indicator		LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted	
Electrical specifications			
Operating voltage	U_B	20 250 V AC/DC	
No-load supply current	I ₀	< 2.5 mA	
Output			
Switching type		dark-on	

4-
ᆽ
≐
6
ō.
72
979
9
e
a
22
ē
蘆
8
Ξ
d
022
2022
ca
ω
귰
ssue
=
0
æ
at
ω
-18
÷
$\overline{}$
Ċ
2022
ĸ
te
dat
Se
eas
æ
Œ

Technical Data			
Signal output		N-channel MOSFET, short circuit protected	
Switching voltage		max. 250 V AC/DC	
Switching current		max. 200 mA	
Voltage drop	U_{d}	≤ 3.5 V AC/DC	
Switching frequency	f	50 Hz	
Response time		≤ 10 ms	
Conformity			
Product standard		EN 60947-5-2	
Compliance with standards and directives			
Standard conformity			
Standards		UL 508	
Approvals and certificates			
Protection class		II, rated insulation voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1	
UL approval		cULus Listed, Type 1 enclosure	
CCC approval		Certified by China Compulsory Certification (CCC)	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-40 70 °C (-40 158 °F)	
Mechanical specifications			
Degree of protection		IP67	
Connection		Micro AC connector, 1/2" V124 ; 4-pin	
Material			
Housing		PC-PBT	
Optical face		PMMA	
Mass		approx. 10 g	

Connection Assignment






Connection Assignment




Wire colors

1 | RD/BK (red/black) 2 | RD/WH (red/white) 3 | RD (red) 4 | GN (green)


Assembly






1	_		
	1	Operating display	green
	2	Signal display	yellow
	4	Emitter	
	5	Receiver	

Characteristic Curve





Accessories

0	CPZ18B03	Mounting Bracket with swivel nut
	BF 18	Mounting flange, 18 mm
5	BF 18-F	Plastic mounting adapter, 18 mm
100	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm
	V124-G-YE2M-PVC	Connecting cable, 1/2" - 20 UNF, 4-pin, PVC cable
	V124-W-YE2M-PVC	Connecting cable, 1/2" - 20 UNF, 4-pin, PVC cable