

Slot grid sensor RAL100-IR/32/98



- Compact slot grid sensor
- Open frame with wide detection area
- Optimized for the detection of small parts
- Option to suppress stationary objects
- Detection of very small guided and non-guided parts in free fall


Compact slot grid sensor, optimized for detection of small parts, 100 mm slot width, infrared light, PNP output, M8 plug




Function

Slot grid sensors are ideal for filling and counting objects in feed devices. In contrast to standard photoelectric slot sensors, the slot grid sensors have an entire field for object detection with a maximum response time of 100 µs and a minimum object size of 1 mm. When using dynamic mode, only moving objects are detected.

Dimensions





Technical Data


General specifications

Light source IRED



Technical Data Light type modulated infrared light CE Marking 100 mm Slot width Slot depth 98 mm Ambient light limit 10000 Lux 2 mm Resolution Temperature influence < 10 % active zone 100 mm x 94 mm Indicators/operating means Function indicator LED, yellow Control elements sensitivity adjustment Control elements Time adjuster for Pulse stretching and Dynamic/static operation **Electrical specifications** 24 V DC \pm 20 % Operating voltage U_B No-load supply current I_0 < 70 mAOutput Switching type dark-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC 200 mA Switching current Voltage drop U_{d} < 2.5 V Switching frequency 5000 Hz Repeat accuracy R 0.1 mm Pulse extension 0.1 ... 150 ms Conformity Product standard EN 60947-5-2 **Ambient conditions** Ambient temperature -10 ... 60 °C (14 ... 140 °F) **Mechanical specifications** Housing length 135 mm 20 mm Housing width Housing height 140 mm Degree of protection Connection M8 connector, 3-pin Material black anodized aluminum Housing Optical face glass 400 g Mass

Connection Assignment



- O = Light on
- = Dark on


Connection Assignment



Wire colors in accordance with EN 60947-5-2

1 BN (brown) 3 BU (blue) 4 BK (black)

Assembly



- 1 Functional display yellow
- 2 Time/static
- 3 Sensitivity adjuster

The information on the maximum resolution (smallest detectable object) relates to the center of the slot grid sensor.

Configuration information

The device is set to large parts by turning the sensitivity adjustment potentiometer clockwise and to small parts by turning the sensitivity adjustment potentiometer counterclockwise.

The "time/static" potentiometer can be used both to select pulse extension in dynamic operation and to select static/dynamic operation. Static operation is selected by turning the potentiometer counterclockwise as far as it will go. Pulse extension is set to 1 ms. Pulse extension can be adjusted between 150 ms and 0 ms by turning the potentiometer clockwise.

In static operation, the output remains set while the object is within the frame. The switching threshold is not automatically tracked in this operating mode. Temperature fluctuations and dirt may trigger a switching operation.

In dynamic operation, the output is set only to the specified pulse extension. Objects that extend into the frame are hidden. If the device becomes dirty in dynamic operation, the output is set statically at 50% reception signal.