



# Diffuse mode sensor WTS10-12/20/105



- Specifically for quality checks on welding caps
- Upper and lower welding caps checked simultaneously
- High position and angle tolerance insensitivity of the welding cap
- Stability alarm indication
- Scratch resistant mineral glass lens

### Diffuse mode sensor









#### **Function**

The welding tip sensor WTS10 series is a contrast evaluation sensor with a large and homogeneous light spot fitted to check the quality of the welding cap's face after milling of the welding tip and which is widely used for industrial welding robots.


After the milling process of the welding cap, both tips of the welding gun are inspected and defects such as inclusions, faulty milling or burrs are


Simultaneous control of the quality of both welding tip caps with one sensor is possible by providing two optical outputs on either side of the

sensor housing.

The WTS10 features an extended detection area of 11 mm diameter, an uniform lightspot over the full sensing range due to coaxial optics beam path, a new display concept, high switching accuracy, a homogenous light spot and improved position and tilting angle tolerance.

### **Dimensions**





		1	1	-
IAC	nn	ıca	<b>L</b> -1	
		IUGI	 ( • I	


General specifications		
Detection range		2 12 mm
Reference target		Copper welding-electrode Diameter: 16 mm , Front end: 6 mm
Light source		LED
Light type		modulated visible red light , 640 nm
Ambient light limit		continuous light 40000 Lux, Modulated light 5000 Lux
Tilting angle		± 1.5 °
Position tolerance		± 2 mm
Indicators/operating means		
Operation indicator		LED green: Power on
Function indicator		LED yellow: switching state LED red: Stability alarm indicator
Teach-In indicator		LED, green/yellow flashing (approx. 4 Hz) Teach Error:LED green/yellow non equiphase flashing; 8.0 Hz
Control elements		Teach-In key
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC
No-load supply current	$I_0$	≤ 70 mA
Output		
Switching type		light-on
Signal output		2 switch outputs PNP, NO short-circuit protected reverse polarity protected
Switching current		max. 100 mA
Switching frequency	f	100 Hz

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 200958\_eng.pdf

Technical Data	
Response time	5 ms
Conformity	
Product standard	EN 60947-5-2
Compliance with standards and directives	
Standard conformity	
Shock and impact resistance	IEC / EN 60068. half-sine, 50 g in each X, Y and Z directions
Vibration resistance	IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions
Approvals and certificates	
Protection class	II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval	cULus Listed
CCC approval	CCC approval / marking not required for products rated ≤36 V
Ambient conditions	
Ambient temperature	0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not varies more than $\pm 7$ °C
Storage temperature	-20 70 °C (-4 158 °F)
Mechanical specifications	
Degree of protection	IP67
Connection	5-pin, M12 x 1 connector
Material	
Housing	PC + ABS
Optical face	Scratch resistant mineral glass lens
Mass	80 g

## **Connection Assignment**





- O = Light on
- = Dark on

### **Connection Assignment**




### **Connection Assignment**

Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)


### **Assembly**



1	LED Power On	green		
2	LED channel I	red		
3	LED channel I	yellow		
4	Teach-In channel I			
5	LED channel II	yellow		
6	LED channel II red			
7	Teach-In channel II			

### **Characteristic Curve**





### Teach-In

- 1. Position the reference welding cap in front of the optical system of the desired sensor channel (channel I or channel II).
- 2. Press and hold the corresponding teach-in button. The sensor confirms the keystroke by the green signal indicator being extinguished briefly (200 ms). After 2 s the sensor switches to teach-in mode: both switching outputs are deactivated. The sensor is taught the properly milled welding cap as a reference sample for the selected sensor channel.
- 3. When the green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash simultaneously, release the teach-in button. Teach-in is completed. The green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash alternately for 2 s.

**Teach-in successful:** The taught reference welding cap is permanently saved. The sensor switches back to switching mode. **Teach-in unsuccessful:** The green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash quickly (approx. 8 Hz) and alternately for 5 s. The sensor discards the taught values. After 5 s the sensor switches to switching mode and works with the last valid values. For signal levels below the fixed switching threshold, the teach-in mode can't be entered. A teach-in error is indicated.

#### **Accessories**

	OMH-WTS10-01	Mounting bracket for sensors of WTS10 series
6/	V15-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
6/	V15-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 5-pin, PUR cable grey
6/	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey