

# Retroreflective sensor

# ML9-54-G/25/136/115a



- Ultra bright LEDs for power on, weak signal indication and switching state
- Flashing power on LED in case of short-circuit
- **TEACH-IN**
- Automatic adjustment in case of soiling in contrast detection
- Not sensitive to ambient light, even with switched energy saving
- Protected against mutual interference (no cross-talk)
- Protection class II

Retroreflective sensor with polarization filter for clear object detection










## **Dimensions**



#### **Technical Data**

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 194196\_eng.pdf


| General specifications    |   |  |
|---------------------------|---|--|
| Effective detection range | 0 3.5 m in TEACH mode<br>0 5.7 m in normal mode |  |
| Reflector distance        | 0 3.5 m in TEACH mode 0 5.7 mm in normal mode   |  |
| Threshold detection range | 7.6 m   |  |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

| Technical Data                       |                |  |
|--------------------------------------|----------------|--|
| Reference target                     |                | H85-2 reflector  |
| Light source                         |                | LED  |
| Light type                           |                | modulated visible red light, 660 nm  |
| Polarization filter                  |                | yes  |
| Angle deviation                      |                | max. ± 1°  |
| Diameter of the light spot           |                | approx. 40 mm at detection range 1 m   |
| Opening angle                        |                | 1.7°   |
| Ambient light limit                  |                | 40000 Lux  |
| Functional safety related parameters |                | 10000 Eux  |
| MTTF <sub>d</sub>                    |                | 1050 a   |
| Mission Time (T <sub>M</sub> )       |                | 20 a   |
| ,,                                   |                |  |
| Diagnostic Coverage (DC)             |                | 0 %  |
| Indicators/operating means           |                |  |
| Operation indicator                  |                | LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) |
| Function indicator                   |                | LED yellow: switching state; Operating reserve; Teach-In   |
| Control elements                     |                | Teach-In key   |
| Contrast detection levels            |                | 10 % - clean, water filled PET bottles   |
| Electrical specifications            |                |  |
| Operating voltage                    | U <sub>B</sub> | 10 30 V DC , class 2   |
| Ripple                               |                | max. 10 %  |
| No-load supply current               | Io             | < 20 mA at 24 V DC   |
| Output                               |                |  |
| Switching type                       |                | light-on   |
| Signal output                        |                | 2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected   |
| Switching voltage                    |                | max. 30 V DC   |
| Switching current                    |                | max. 100 mA  |
| Switching frequency                  | f              | 1000 Hz  |
| Response time                        |                | 500 μs   |
| Conformity                           |                |  |
| Product standard                     |                | EN 60947-5-2   |
| Approvals and certificates           |                |  |
| Protection class                     |                | II, rated voltage ≤ 50 V AC with pollution degree 1-2 according to IEC 60664-1 functional insulation acc. to DIN EN 50178                            |
| UL approval                          |                | cULus  |
| CCC approval                         |                | CCC approval / marking not required for products rated ≤36 V   |
| Ambient conditions                   |                |  |
| Ambient temperature                  |                | -20 60 °C (-4 140 °F)  |
| Storage temperature                  |                | -40 75 °C (-40 167 °F)   |
| Mechanical specifications            |                |  |
| Housing width                        |                | 23 mm  |
| Housing height                       |                | 38 mm  |
| Housing depth                        |                | 11 mm  |
|                                      |                | IP67   |
| Degree of protection                 |                |  |
| Connection                           |                | 200 mm fixed cable with 4-pin, M8x1 connector  |
| Material                             |                |  |
| Housing                              |                | PC (glass-fiber-reinforced Makrolon)   |
| Optical face                         |                | glass  |
| Mass                                 |                | approx. 25 g   |

**5**PEPPERL+FUCHS

## Connection



- O = Light on
- = Dark on


# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


ΒN (brown) 2 WH (white) 3 BU (blue) BK (black)


# Assembly




| 1 | LED green  |
|---|------------|
| 2 | LED yellow |
| 3 | Teach-In   |

#### **Characteristic Curve**







## **Accessories**

|    | OMH-ML9       | Mounting aid for ML9 series, Mounting bracket                          |
|----|---------------|--|
|    | OMH-ML9-01    | Mounting aid for ML9 series, Threaded bolt M3                          |
| 6/ | V31-GM-2M-PVC | Female cordset single-ended M8 straight A-coded, 4-pin, PVC cable grey |
| 6/ | V31-WM-2M-PVC | Female cordset single-ended M8 angled A-coded, 4-pin, PVC cable grey   |
| 6/ | V31-GM-5M-PUR | Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey |
| 6/ | V31-WM-5M-PUR | Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey   |

## **Adjustment instructions**

#### Adjustment instructions for devices with Teach-In

After the operating voltage has been applied, the LED is lit green. The sensor is automatically set to a state of maximum sensitivity (state as supplied) or the state of the most recent Teach-In setting.

Assemble the appropriate reflector opposite the light barrier.

#### Teach-In using the Teach key

- · Align the sensor to an appropriate reflector.
- Press the Teach key as confirmation, the green display LED is briefly turned off once.
- Hold the Teach key down until the yellow and green display LED is flashing at regular intervals (about 2.5 Hz).
  Then release the Teach key.
- During the internal set-up of the sensor, the green and yellow display LEDs flash alternately (about 2.5 Hz).
- Teach-In successful: The green and yellow display LEDs are lit. Contrast detection 10% is activated. The device is ready for operation.
- Teach-In not successful: The green and yellow display LEDs flash alternately and rapidly (about 8 Hz) for about 5 seconds. Then the sensor goes to the state with maximum sensitivity.
  - After this happens, repeat the Teach-In procedure, starting with step 1.