

# **SMART Transmitter Power Supply** KFD2-STC5-2

- 2-channel signal conditioner
- 24 V DC supply (Power Rail)
- Input 2-wire and 3-wire SMART transmitters and 2-wire SMART current sources
- Output 4 mA ... 20 mA current sink/current source
- Terminals with test points
- Up to SIL 2 acc. to IEC/EN 61508

# **( € SIL 2**

#### **Function**

This signal conditioner provides the galvanic isolation between field circuits and control circuits.

The device supplies 2-wire and 3-wire SMART transmitters, and can also be used with 2-wire SMART current sources.

It transfers the analog input signal as an isolated current value.

Digital signals may be superimposed on the input signal on the field side or on the control side and are transferred bi-directionally.

The device provides a sink mode or a source mode output on the control side terminals.


The device has an internal resistor. Use this resistor if the HART communication resistance in the control circuit is too low. Test sockets for the connection of HART communicators are integrated into the terminals of the device.

#### Application

The device supports the following SMART protocols: • HART

- BRAIN
- Foxboro

#### **Connection**



## **Technical Data**

| General specifications               |              |
|--------------------------------------|--------------|
| Signal type                          | Analog input |
| Functional safety related parameters |              |
| Safety Integrity Level (SIL)         | SIL 2        |
| Supply                               |              |



| Technical Data                             |                |  |
|--|----------------|--|
| Connection                                 |                | Power Rail or terminals 14+, 15-   |
| Rated voltage                              | U <sub>r</sub> | 18 30 V DC   |
| Ripple                                     | J <sub>r</sub> | within the supply tolerance  |
| Power dissipation                          |                | ≤ 1.4 W at maximum load  |
| Power consumption                          |                | ≤ 2.6 W at maximum load  |
| Input                                      |                | S 2.0 W at maximum load  |
| Connection side                            |                | field side   |
| Connection                                 |                | terminals 1+, 2-, 3; 4+, 5-, 6   |
| Input signal                               |                | 4 20 mA  |
| Open circuit voltage/short-circuit current |                | terminals 1+, 3; 4+, 6: 23 V / 25 mA   |
| Input resistance                           |                | max. 265 Ω terminals 2-, 3; 5-, 6 , max. 330 Ω terminals 1+, 3; 4+, 6  |
| Available voltage                          |                | $\geq$ 16 V at 20 mA; $\geq$ 20 V at 4 mA, terminals 1+, 3; 4+, 6  |
| Output                                     |                | 2 10 V at 20 111A, 2 20 V at 4 111A, terminals 1+, 5, 4+, 0  |
| Connection side                            |                | control side   |
| Connection                                 |                |  |
| Connection                                 |                | terminals 7+, 8-, 9-; 10+, 11-, 12- (sink)<br>terminals 7-, 8+, 9+; 10-, 11+, 12+ (source)<br>see additional information   |
| Load                                       |                | 0 600 Ω  |
| Output signal                              |                | 4 20 mA (overload > 25 mA)   |
| Ripple                                     |                | max. 50 $\mu$ A <sub>rms</sub>   |
| External supply (loop)                     |                | 2 30 V DC If the external voltage is > 19 V, a load $\geq$ ((V - 19) / 0.02) $\Omega$ is required. V represents the value of the external voltage. The internal 250 $\Omega$ resistor at terminals 9 and 12 can be used as a load. |
| Transfer characteristics                   |                |  |
| Deviation                                  |                | at 20 °C (68 °F), 4 20 mA $\leq$ 10 $\mu A$ incl. calibration, linearity, hysteresis, loads and fluctuations of supply voltage   |
| Influence of ambient temperature           |                | ≤ 0.25 µA/K  |
| Frequency range                            |                | field side into the control side: band width with 1 $V_{pp}$ signal 0 7.5 kHz (-3 dB) safe area to hazardous area: band width with 1 $V_{SS}$ signal 0.3 7.5 kHz (-3 dB)   |
| Settling time                              |                | 200 μs   |
| Rise time/fall time                        |                | 100 μs   |
| Galvanic isolation                         |                |  |
| Input/Output                               |                | basic insulation according to IEC 61010-1, rated insulation voltage 300 $\ensuremath{V_{\text{eff}}}$  |
| Input/power supply                         |                | basic insulation according to IEC 61010-1, rated insulation voltage 300 $\ensuremath{V_{\text{eff}}}$  |
| Output/power supply                        |                | functional insulation, rated insulation voltage 50 V AC  |
| Output/Output                              |                | functional insulation, rated insulation voltage 50 V AC  |
| Indicators/settings                        |                |  |
| Display elements                           |                | LED  |
| Labeling                                   |                | space for labeling at the front  |
| Directive conformity                       |                |  |
| Electromagnetic compatibility              |                |  |
| Directive 2014/30/EU                       |                | EN 61326-1:2013 (industrial locations)   |
| Conformity                                 |                |  |
| Electromagnetic compatibility              |                | NE 21:2012<br>EN 61326-3-2:2008  |
| Degree of protection                       |                | IEC 60529:2001   |
| Protection against electrical shock        |                | UL 61010-1:2012  |
| Ambient conditions                         |                |  |
| Ambient temperature                        |                | -20 70 °C (-4 158 °F)  |
| Mechanical specifications                  |                |  |
| Degree of protection                       |                | IP20   |
| Connection                                 |                | screw terminals  |
| Mass                                       |                | approx. 150 g  |
| Dimensions                                 |                | 20x124x115 mm (0.8 x 4.9 x 4.5 inch) (W x H x D) , housing type B2   |
| Mounting                                   |                | on 35 mm DIN mounting rail acc. to EN 60715:2001   |



**5**PEPPERL+FUCHS

## **Technical Data**


#### **General information**

Supplementary information

Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

## **Assembly**

#### Front view



## **Matching System Components**

| KFD2-EB2         | Power Feed Module   |
|------------------|---|
| UPR-03           | Universal Power Rail with end caps and cover, 3 conductors, length: 2 m       |
| UPR-03-M         | Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m     |
| UPR-03-S         | Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m     |
| K-DUCT-GY        | Profile rail, wiring comb field side, gray                                    |
| K-DUCT-GY-UPR-03 | Profile rail with UPR-03-* insert, 3 conductors, wiring comb field side, gray |

## **Accessories**

Release date: 2023-06-05 Date of issue: 2023-06-05 Filename: 203646\_eng.pdf

| 1 | K-250R    | Measuring resistor |
|---|-----------|--------------------|
| 1 | K-500R0%1 | Measuring resistor |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

## **Accessories** KF-ST-5GN Terminal block for KF modules, 3-pin screw terminal, green KF-STP-5GN Terminal block for KF modules, 3-pin screw terminal, with test sockets, green KF-CP Red coding pins, packaging unit: 20 x 6