



## Connector box for barcode scanner **CBX100**

- Connect up to 32 scanners to a network with ID-Net<sup>TM</sup>
- Option of upgrading with memory module
- Easy scanner connection by means of clamp terminals
- Degree of protection IP65

Connector box for barcode scanner



## **Function**


Devices from the CBX\* series enable barcode scanners to be connected quickly and easily. A wide variety of connections also allows other field devices to be connected.


By reducing installation time and the number of system failures when a device is replaced, your operating costs will be significantly lower. Standardized pinning of connections and simple attachment of cable ends using spring terminals ensures easy cable installation. The


configuration of the connected scanner can be saved in backup modules and restored at a later date.


To facilitate installation of the device, the continuous mounting holes are easy to access and the top section of the housing can be removed. Note: Avoid mechanical stress, such as screwing the housing cover together, in deep-freeze areas.

## **Dimensions**











		1	1	-
IAC	nn	ıca	<b>L</b> -1	
		IUGI	 ( • I	

Indicators/operating means		
Display elements		5 LEDs (POWER, TRIGGER, IN 2, OUT 1, OUT 2)
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC
Current consumption		max. 2.5 A
Power consumption	$P_0$	max. 3 W
Compliance with standards and directives		
Directive conformity		89/336 EWG
Standard conformity		
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007
Noise immunity		EN 61000-6-2
Degree of protection		EN 60529
Ambient conditions		
Ambient temperature		-35 50 °C (-31 122 °F) Mount, connect, and configure only between 0° 50°
Storage temperature		-20 70 °C (-4 158 °F)
Relative humidity		90 % , noncondensing
Shock resistance		EN 60068-2-27 30G 11 ms; 3 impacts on each axis
Vibration resistance		EN 60068-2-6 1.5 mm 10 55 Hz ; 2 hours on each axis
Mechanical specifications		
Degree of protection		IP65
Connection		25-pin Sub-D socket for Barcode scanner , M16 cable gland for system connection $(4x)$

Material	
Housing	PC (Polycarbonate)
Mass	380 g

## Connection





- Power Switch (on/off)
- Serial Interface (SUB-D, 9-pin)
- Mounting Holes (2x)
- **ID-NET Terminator Switch**
- LEDs
- Backup Module connector
- Terminal Block

- (8) RS485 Terminator Switch
- (9) External Power Source (on/off)
- Adjustment of Shield to Protection Earth via Jumper
  - Adjustment of Chassis Grounding via Jumper