Connector box for barcode scanner

CBX500



- Connect up to 32 scanners to a network with ID-NetTM
- Option of upgrading with Profibus, Ethernet and DeviceNet module as well as memory module
- Easy scanner connection by means of clamp terminals
- Degree of protection IP65

Connector box for barcode scanner

0000


Function


Devices from the CBX* series enable barcode scanners to be connected quickly and easily. A wide variety of connections also allows other field devices to be connected.


By reducing installation time and the number of system failures when a device is replaced, your operating costs will be significantly lower. Standardized pinning of connections and simple attachment of cable ends using spring terminals ensures easy cable installation. The configuration of the connected scanner can be saved in backup modules and restored at a later date.

To facilitate installation of the device, the continuous mounting holes are easy to access and the top section of housing can be removed.

Dimensions








4

Technical Data Indicators/operating means 5 LEDs (POWER, TRIGGER, IN 2, OUT 1, OUT 2) Display elements **Electrical specifications** U_B 10 ... 30 V DC PELV Operating voltage Current consumption max. 2.5 A max. 3 W Power consumption Interface Interface type Modular upgrade option (e.g. PROFIBUS, Ethernet, DeviceNet) Compliance with standards and directives Directive conformity 89/336 EWG Standard conformity Noise immunity EN 61000-6-2 EN 60529 Degree of protection Shock and impact resistance EN 60068-2-27 Vibration resistance EN 60068-2-6 **Ambient conditions** Ambient temperature 0 ... 50 °C (32 ... 122 °F) Storage temperature -20 ... 70 °C (-4 ... 158 °F) Relative humidity 90 %, noncondensing Shock resistance 30G; 11 ms; 3 impacts on each axis Vibration resistance 1.5 mm; 10 ... 55 Hz; 2 hours on each axis **Mechanical specifications** IP65 Degree of protection 25-pin Sub-D socket for Barcode scanner, M16 cable gland for system connection Connection Material Housing PC (Polycarbonate) Mass 780 g



- 1 Power switch (on/off)
- Adjustment of Chassis grounding via Jumper
- 3 Mounting Holes (2x)
- 4 Remote I/O Extension Module Connector
- Backup Module Connector
- (6) LEDs
- 7 RS485 Terminator Switch

- (8) ID-NET Terminator Switch
- 9 Serial Interface (SUB-D, 9-pin)
- 10 IP65 Fieldbus Module Connector
- (11) Standard Fieldbus Module Connector
- (12) Terminal Block
- Adjustment of Shield to Protection Earth via Jumper
- (14) External Power Source (on/off)