



# **Model Number**

GLP30-RT/40b/103/156

Photoelectric slot sensor with 3-pin, M8 x 1 connector


# **Features**

- Plastic version •
- Clearly visible function indicators ٠
- Degree of protection IP67 •


### **Product information**


An extremely favorable price/performance ratio and an innovative display concept characterize the GLP series. The switching states are visible from all directions. The optional attachment holes or dove tail joint significantly increase installation flexibility. The external, dynamic Teach-In function allows you to teach in moving objects easily.






Туре	A	В	С	D	E	F	G	Number of mounting holes M4 *
GLP30-RT-	30	50	30	34	59.5	20	-	1
GLP50-RT-	50	70	50	54	79.5	20	28	2
GLP80-RT-	80	100	80	54	79.5	20	2 x 28	3
GLP120-RT-	120	140	120	54	79.5	20	3 x 28	4






### **Electrical connection**




Pinout



# (brown) (blue) (black)

# Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Emitter	
5	Receiver	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

<sup>5</sup> PEPPERL+FUCHS

Technical data					
General specifications					
Light source		LED , 640 nm pulsing			
Light type		modulated visible red light			
Object size		min. 0.3 mm			
Slot width		30 mm			
Slot depth		34 mm			
Ambient light limit		10000 Lux			
Indicators/operating means					
Function indicator		LED yellow , lit when the light beam is interrupted LED green: ready			
Control elements		Teach-In key , Sensitivity adjustment and Mode adjustment (NO/NC)			
Electrical specifications					
Operating voltage	UB	10 30 V DC			
Ripple		10 %			
No-load supply current	I <sub>0</sub>	≤ 30 mA			
Output					
Switching type		light/dark on			
Signal output		1 PNP, short-circuit protected, reverse polarity protected, open collector			
Switching voltage		max. 30 V DC			
Switching current		max. 100 mA			
Voltage drop	U <sub>d</sub>	≤ 2.4 V			
Switching frequency	f	2000 Hz			
Response time		0.25 ms			
Conformity					
Product standard		EN 60947-5-2			
Ambient conditions					
Ambient temperature		-20 60 °C (-4 140 °F)			
Storage temperature		-20 80 °C (-4 176 °F)			
Mechanical specifications					
Degree of protection		IP67			
Connection		M8 connector, 3-pin			
Material					
Housing		PC			
Optical face		plastic			
Mass		20 g			
Approvals and certificates					
Protection class		II			
UL approval		cULus Listed, Class 2 Power Source "For use in NFPA 79 Applications only" Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.			
			£		

### Accessories

**OMH-K03** dove tail mounting clamp

**V3-WM-2M-PUR** Female cordset single-ended, M8, 3-pin, PUR cable

V3-GM-BK2M-PUR-U <sup>-</sup>emale cordset single-ended, M8, 3-pin,

PUR cable

## V3-WM-BK2M-PUR-U

Female cordset single-ended, M8, 3-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

Pepperl+Fuchs Group www.pepperl-fuchs.com

2

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

76 1111 Singapo uchs.com fa-info@sg.j