



## **Model Number**

#### GLP80-RT/40b/102/156

Photoelectric slot sensor with 3-pin, M8 x 1 connector


#### **Features**

- Plastic version
- · Clearly visible function indicators
- · Degree of protection IP67


# **Product information**

An extremely favorable price/performance ratio and an innovative display concept characterize the GLP series. The switching states are visible from all directions. The optional attachment holes or dove tail joint significantly increase installation flexibility. The external, dynamic Teach-In function allows you to teach in moving objects easily.

### **Dimensions**



## **Electrical connection**



- O = Light on
- = Dark on


### **Pinout**

Wire colors in accordance with EN 60947-5-2



BN (brown) BU (blue) BK (black)

## Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Emitter	
5	Receiver	

Technical data					
General specifications					
Light source		LED , 640 nm pulsing			
Light type		modulated visible red light			
Object size		min. 0.5 mm			
Slot width Slot depth Ambient light limit		80 mm 54 mm			
					10000 Lux
		Indicators/operating means			
Function indicator		LED yellow , lit when the light beam is interrupted LED green: ready			
Control elements		Teach-In key , Sensitivity adjustment and Mode adjustment (NO/NC)			
Electrical specifications					
Operating voltage	$U_B$	10 30 V DC			
Ripple		10 %			
No-load supply current	I <sub>0</sub>	≤ 30 mA			
Output					
Switching type		light/dark on			
Signal output		1 NPN short-circuit protected, reverse polarity protected, open collector			
Switching voltage		max. 30 V DC			
Switching current		max. 100 mA			
Voltage drop	$U_d$	≤ 2.4 V			
Switching frequency	f	2000 Hz			
Response time		0.25 ms			
Conformity					
Product standard		EN 60947-5-2			
Ambient conditions					
Ambient temperature		-20 60 °C (-4 140 °F)			
Storage temperature		-20 80 °C (-4 176 °F)			
Mechanical specifications					
Degree of protection		IP67			
Connection		M8 connector, 3-pin			
Material					
Housing		PC			
Optical face		plastic			
Mass		35 g			
Approvals and certificates					
Protection class		II			
UL approval		cULus Listed, Class 2 Power Source "For use in NFPA 79 Applications only" Adapters providing field wiring means are available from the			

# Accessories

### OMH-K03

dove tail mounting clamp

### V3-WM-2M-PUR

Female cordset single-ended, M8, 3-pin, PUR cable

### V3-GM-BK2M-PUR-U

Female cordset single-ended, M8, 3-pin, PUR cable

## V3-WM-BK2M-PUR-U

Female cordset single-ended, M8, 3-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

**FPEPPERL+FUCHS** 

manufacturer. Refer to manufacturers information.